




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
Mating Tab Width: **2.8 mm [.11 in]**
Mating Tab Thickness: **.51 mm [.019 in]**
PCB Hole Diameter: **3.68 mm [.145 in]**
Termination Method to PCB: **Through Hole - Screw**

Features

Industry Standards

Compatible With Agency/Standards Products	CSA
---	-----

Product Type Features

Terminal Features	Stud Hole
-------------------	-----------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Dimensions

Stud Diameter	3.68 mm[.145 in]
PCB Hole Diameter	3.68 mm[.145 in]

Contact Features

--	--



PCB Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.51 mm[.019 in]
Terminal Plating Material	Unplated
Contact Underplating Material	None
Terminal Size	2.8
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Screw
Product Terminates To	Printed Circuit Board

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63633-1 250 FASTON TAB BR	 TE Part # 42822-4 250 FASTON TAB TPBR	 TE Part # 62628-1 100 FASTON TAB TPST	 TE Part # 62629-2 110 FASTON TAB BR
 TE Part # 60613-1 205 FASTON TAB BR	 TE Part # 62061-1 110 FASTON TAB BR	 TE Part # 735187-2 110 FASTON TAB TPBR	 TE Part # 62298-1 187 FASTON TAB BR
 TE Part # 62061-2 110 FASTON TAB BR	 TE Part # 62576-1 187 FASTON TAB BR	 TE Part # 62836-1 110 FASTON TAB TPBR	 TE Part # 60443-1 187 FASTON TAB BR


Also in the Series | FASTON 110

 Crimp Terminal Housings(13)	 Insertion & Extraction Tools(1)	 PCB Terminals(22)	 Quick Disconnects(168)
--	--	--	---

Customers Also Bought



TE Part #292303-3
Std USB Type A, R/A, T/H, Natural



TE Part #280610-1
4P MOD 1 SHROUDED HEADER, ST, TIN PLTD



TE Part #58579-1
MTA 100 MANUAL TOOL ASSEMBLY DISCRETE



TE Part #1571100-2
PRCSD1-20F-BB0DW, POWER ROCKER DISCRETE



TE Part #1-1478966-0
SMA B/HD SKT RCPT GSS



TE Part #CV3299-000
RW-175-3/64-X-STK



TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #60214-3
187 FASTON REC 20-16 AWG BR



TE Part #1337815-3
50 OHM COAX SMB STR PLUG STR P

Documents

Product Drawings
110 FASTON TAB BR

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_62628-2_M.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_62628-2_M.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_62628-2_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



FASTON Tabs

English