



MTA 100

TE Internal #: 3-644512-4
Connector Assembly, Receptacle, Insulation Displacement (IDC),
Wire-to-Board, Tin, Normal, UL 94V-2, MTA 100, Standard
Rectangular Connectors

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

[All Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100 \(127\)](#)

Features

Packaging Features

Packaging Quantity	2200
Packaging Method	Reel

Dimensions

Product Width	6.99 mm[.275 in]
Product Length	10.16 mm[.4 in]
Connector Height	13.21 mm[.52 in]
Wire Size	24 AWG

Housing Features

Housing Material	Nylon 6/6
Housing Color	White
Centerline (Pitch)	2.54 mm[.1 in]

Configuration Features

--	--



Number of Cavities	4
Contacts Preloaded	Yes
Number of Positions	4
Number of Rows	1

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	LR 7189
UL Flammability Rating	UL 94V-2

Contact Features

Contact Underplating Material	Nickel
Wire Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Mating Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Wire & Cable



Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



Also in the Series | MTA 100

Connector Caps & Covers(69)	Connector Contacts(8)	Connector Hardware(1)	Insertion & Extraction Tools(2)
PCB Headers & Receptacles(441)	Standard Rectangular Connectors(495)	Wire-to-Board Connector Assemblies & Housings(1)	Wire-to-Board Headers & Receptacles (441)

Customers Also Bought

TE Part #3-644312-4 04P MTA100 CONN ASSY BLK LF	TE Part #2-1676480-2 CRG0402 1% 1K0	TE Part #4-2176339-7 CRGCQ 0603 68K 1%	TE Part #3-1623925-2 CFR100 5% 33K
TE Part #1-1676480-0 CRG0402 1% 130K	TE Part #7-1676480-4 CRG0402 1% 560R	TE Part #6-2176309-1 RP 1E 0.1W 42R2 0.1% 25PPM 1K RL	TE Part #5052892055 RNF-100-1/16-0-STK
TE Part #87499-3 02 MODIV HSG SR MRKD .100CL	TE Part #167022-3 MOD-5 REC.CONTACT		



Documents

Product Drawings

04P MTA100 CONN ASSY TAPE LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-644512-4_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-644512-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-644512-4_M.3d_stp.zip

English

Customer View Model

ENG_CVM_3-644512-4_H.3d_igs.zip

English

Customer View Model

ENG_CVM_3-644512-4_H.3d_stp.zip

English

Customer View Model

ENG_CVM_3-644512-4_H.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English