




PIDG

TE Internal #: 323916  
Closed Ring Tongue Terminal, 26 – 22 AWG, #8 / M4 Stud, 4.34 mm [.171 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: #8, M4

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.302 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1
Packaging Method	Loose Piece

Product Type Features



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	18.8 mm[.74 in]
Compatible Insulation Diameter (Max)	2.08 mm[.082 in]
Compatible Insulation Diameter Range	1.27 – 2.08 mm[.05 – .082 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 69344  
PIDG 26-22 DIE SET

TE Part # 46121  
DAHT PG PIDG 26-22 ASSY

TE Part # 59275  
T-HEAD PIDG PG SH 26-20 ASSY

Also in the Series | PIDG

Compression Connectors(17)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

Quick Disconnects(38)

Ring Terminals(588)

Spade Terminals(228)

Special Purpose Terminals(1)

Splices(41)



Customers Also Bought

TE Part #60789-3  
.058 DIA RECEPTACLE LP 20-24  
GPPHBR

TE Part #926898-3  
UNIV.M-N-L.PIN

TE Part #626062  
FASTIN-ON HOUSING REC PA66  
NATURAL

TE Part #164900-5  
LOCK.POST ASSY.KIT

TE Part #925544-2  
FF 110 REC 0.5-1.5MM2 PB LP

TE Part #8-1879221-1  
CPF 0603 10R7 0.1% 25PPM 1K RL

TE Part #024311-000  
55FA0514-24-7L

TE Part #1337775-3  
75 OHM COAX BNC STR PLUG-P99-E

TE Part #Y72428-11-05PNV003  
HERM RECP

TE Part #846013-E  
IDCCS SRC 1,27 2 \* SPX NXX 260 PVC

Documents

Product Drawings  
TERMINAL,PIDG R 26-22 8  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_323916\_N.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_323916\_N.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_323916\_N.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

323916

Closed Ring Tongue Terminal, 26 – 22 AWG, #8 / M4 Stud, 4.34 mm [.171 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG



Datasheets & Catalog Pages  
PIDG TERMINALS & SPLICES Quick Reference Guide  
English