



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .32 – .82 mm²

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Dimensions

Product Length	20.44 mm[.805 in]
Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 152422-1
250 FASTON, TAB, ADAPTER, BR

TE Part # 2063429-1
SDE F FASTON 250 0.35-2.50mm2 ASSY

TE Part # 752856-1
DIES 90166-1

TE Part # 539740-2
DIE F6. 3FF REC.

TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 2063429-2
SDE F FASTON 250 0.35-2.50mm2 DIE SET

TE Part # 575046-1
DAHT 250 FASTON 22-14 ASSY

TE Part # 42025-4
250 FASTON REC 18-16 AWG TPBR

TE Part # 90166-1
DAHT 250 FASTON REC 22-18 ASSY

TE Part # 61873-1
250 FASTON REC 18-14 AWG TPBR

TE Part # 91514-1
CCII FASTON 250 REC 22-18 ASSY

Also in the Series | **FASTON 250**



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)




Quick Disconnects(425)



Splices(4)

Customers Also Bought



TE Part #1-2273002-1
M8 x 1.0 straight plug Pigtail



TE Part #206043-1
RECEPT,SZ 17-14 CPC



TE Part #182649-1
17-14 CPC PLUG RS



TE Part #6-1623930-7
CFR25 5% 2K4




TE Part #5052842031
RNF-100-3/64-0-STK



TE Part #T4061210004-002
M8 CABLE RA M 1.0M 4POS PVC CABLE



TE Part #587763-000
CWT-11-W122-5



TE Part #160739-4
250 FASTON,PIGGYBACK REC.,18-14 AWG,TPPB



TE Part #802427-SF
FN2030-3-06



TE Part #802430-SF
FN2030-6-06

Documents



Product Drawings

250 FASTON REC 22-18 AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_41969-2_AA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_41969-2_AA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_41969-2_AA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Wire Preparation And Crimp Inspection Guide

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Crimping Head for FASTON Terminals

English

Agency Approvals

Agency Approval Document

English