




TE Internal #: 1-6368011-1

RJ45 Connector, Multiple Ports, 2 x 1, Jack, Shielded, Cat 5, Standard - Latch Down, 8 Position, Low Profile, Through Hole - Solder, Right Angle

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Multiple Ports**

Port Matrix Configuration: **2 x 1**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Packaging Features

Packaging Quantity	180
Packaging Method	Tray

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	31.45 mm[1.23 in]

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Panel Mount, Board Mount

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A, .2 A
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze



Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Body Features	
LED Color (Bottom Left)	Green/Yellow
LED Color (Bottom Right)	Green/Yellow
Grounding Tab Plating Material	Tin over Nickel
Shield Plating Material	Tin over Nickel
Shield Material	Brass
LED Color (Top Right)	Green/Yellow
LED Color (Top Left)	Green/Yellow
Modular Jack Latch Orientation	Standard - Latch Down
Connector Profile	Low
Industry Standards	
UL Flammability Rating	UL 94V-0
Performance Category	Cat 5
Operation/Application	
Indicator Type	LED
Shielded	Yes
Circuit Application	Signal
Configuration Features	
Number of PCB Ground Tabs	6
Multiple Port Configuration	Stacked
Port Configuration	Multiple Ports
Port Matrix Configuration	2 x 1
Connector Contact Density	Standard
Number of Positions	8
Number of Loaded Positions	8
PCB Mount Orientation	Right Angle
Product Type Features	
Connector Product Type	Connector Assembly
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack



Grounding Options	PCB and Panel Ground
Connector & Contact Terminates To	Printed Circuit Board

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Housing Features

Mating Entry Location	Side
Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Black
Housing Material	PBT Polyester

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 188729-1  
8P.COVER/SOLD.STOP

Customers Also Bought



TE Part #1-2199230-6  
M.2 0.5PITCH 4.2H KEY M 30U AU



TE Part #2198325-6  
zSFP+ STACKED 2X2 RECEPTACLE ASSEMBLY



TE Part #2065657-1  
zd Plus, 4 pair, receptacle assy



TE Part #6339488-1  
VERTICAL BATTERY CONNECTOR ASSY



TE Part #2174507-2  
MICRO USB, TYPE B



TE Part #5104338-7  
A/L LOW PRO HDR 34P VERT HT



TE Part #5-147291-5  
03 MODII HDR SR SFMT B/A T&R, lead-Free



TE Part #5554517-1  
MJ,R/A,8P/8C,KEYED,TRAY PACK



TE Part #1888972-1  
Cage Assy SAN Hsink LP QSFP Thru Bezel



TE Part #384265-E  
STVB/2 32 M AB VV 4-00 0606 \*\* 247 E007

Documents

Product Drawings  
STK JK,2X1,SHLD,G/Y BI-CLR LED  
English



CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-6368011-1\_D.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-6368011-1\_D.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-6368011-1\_D.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English