




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2.1 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Locking Lance Height	.8 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	21.5 mm[.846 in]
Compatible Insulation Diameter Range	2.9 – 3.8 mm[.114 – .15 in]



Terminal Material Thickness	.33 mm[.013 in]
Wire Size	2.1 – 3.31 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 160950-1
FF 250 REC BR SOLDERING

TE Part # 2150533-1
OCEAN_2.0_Applicator-E-130F180F-REM

TE Part # 2150533-2
OCEAN_2.0_Applicator-E-130F180F-REA

TE Part # 7-2150533-7
OCEAN_2.0_SPARE_PART_KIT-130F180F

TE Part # 1989879-1
.250 SRS FASTIN-ON REC.

TE Part # 2819183-1
.250 SERIES FASTIN FASTON REC.

TE Part # 640841-1
BLADE REC 250 20-16AWG BR

TE Part # 170303-1
FF 250 REC 22-18AWG BR WITH LATCH

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(207)

Insertion & Extraction Tools(2)

PCB Terminals(2)

Quick Disconnects(250)

Customers Also Bought



TE Part #1456471-1
8p Hybrid 0.64/2.8 Unsealed PI

TE Part #170456-2
PL 250 AM REC 12-10 0.40 X 21 PRE-TPBR

TE Part #1393249-7
W58-XB1A4A-10=W58

TE Part #1-1393249-1
W58-XB1A4A-2=W58

TE Part #1123371-1
040-3 MLC PLUG HSG ASSY 16P

TE Part #170089-2
FF 250 REC 14-12AWG TPBR

TE Part #1-2291193-3
SMARTSEAL TERMINAL

TE Part #1674311-7
0.64 III RCPT 3 Serrations Pre-Tin

TE Part #2203771-1
3POS, MCON 1.2 CB REC 1p TL SEALED

TE Part #2305881-1
CVTY PLUG,090 SERIES,CVTY DIA,1, GRY

Documents

Product Drawings
FF 250 REC 14-12AWG BR
Japanese

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_170089-1_P.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_170089-1_P.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_170089-1_P.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Crimping of 250 Series Tab and Receptacle Contacts

Japanese

Application Specification

Japanese

Application Specification

Japanese

Crimping of 250 Series Tab and Receptacle Contacts

Japanese

Agency Approvals

UL Report

English