



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**

Number of Poles: **2**

Primary Product Color: **Gray**

Product Spacing: **5 mm [.197 in]**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

Features

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Electrical Characteristics

Current Rating (IEC)	24 A
----------------------	------

Mechanical Attachment

Tightening Torque	5.31 in-lbs
-------------------	-------------

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Dimensions

Product Width	4.6 mm[.181 in]
Product Depth	22.2 mm[.874 in]
Product Length	22.2 mm[.874 in]
Product Height	4.6 mm[.181 in]



Product Spacing	5 mm[.197 in]
-----------------	---------------

Body Features

Plastic & Resin Material Type	Polyamide
Product Weight	3.95 g[.139 oz]
Primary Product Color	Gray

Product Type Features

Conducting Accessory Type	Jumper Bar
---------------------------	------------

Configuration Features

Number of Poles	2
-----------------	---

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1SNL505010R0000
[C2.5/5](#)

Also in the Series | ENTRELEC SNACOMPACT

Modular Terminal Blocks(23)

Terminal Block & Strip Conducting
Accessories(16)

Terminal Block & Strip Insulating
Accessories(1)

Customers Also Bought

TE Part #9-1419111-1
[PT570730](#)

TE Part #7-1393243-9
[RT424730](#)

TE Part #1956024-4
[V23092-S1024-A301](#)

TE Part #1-1415539-6
[PTMG0220](#)

TE Part #1SNA235545R0000
[PM307](#)

TE Part #1SNL610010R0000
[C10/10](#)

TE Part #1SNL610020R0000
[C10/10.N](#)

TE Part #1SNL612020R0000
[C16/12.N](#)



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNL905602R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNL905602R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNL905602R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SNACOMPACT TERMINAL BLOCKS SCREW CLAMP TECHNOLOGY

English

BJCI5-2

English