




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 6529 – 10382 CMA

Stud Size: #10

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.241 g
----------------	---------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	None



Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Dimensions

Wire Size	6529 – 10382 CMA
Stud Diameter	4.82 mm [.19 in]
Tongue Thickness	1.02 mm [.04 in]
Product Length	17.02 mm [.67 in]
Barrel Inside Diameter	3.05 mm [.12 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150245-2
OCEAN_2.0_Applicator-E-210F-REA



KIT
REPRESENTATION ONLY

TE Part # 7-2150245-7
OCEAN_2.0_SPARE_PART_KIT-210F



TE Part # 2150245-1
OCEAN_2.0_Applicator-E-210F-REM




TE Part # 61546-1
RING TONGUE 10-6 AWG TPCUBR



TE Part # 63526-1
FLANGED SPADE TERMINAL 12-10 AWG BR

Customers Also Bought



TE Part #41495
SPADE .190(4.82 MM)12-10 AWG TPBR



TE Part #63522-1
250 FASTON TAB 20-15 AWG NPST




TE Part #63306-2
250 FASTON REC 18-14 AWG TPBR




TE Part #1217113-2
187 PL MKIII REC. 22-18AWG TPBR



TE Part #61177-2
250 FASTON FLAG REC 18-12 AWG
TPBR



TE Part #62056-6
250 FASTON FLAG REC 18-12 AWG
TPBZ




TE Part #1-330021-0
SPLICE, CE ECON 22-16



TE Part #2-32589-1
TERMINAL, PIDG SPD 12-10 10



TE Part #469004-1
FLOATING SHEAR



TE Part #520935-9
PL&STANDARD FASTON 250
HOUSING REC BLA

Documents

Product Drawings

RING TERMINAL 12-10 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_40524_BF_c-40524-bf.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_40524_BF_c-40524-bf.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_40524_BF_c-40524-bf.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Agency Approvals

CSA Certificate

English