



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Primary Product Material: **Silicone**

Primary Product Color: **Brown**

Cavity Diameter: **3.6 mm [.142 in]**

Compatible Insulation Diameter Range: **2.2 – 3 mm [.087 – .118 in]**

Features

Industry Standards

UL Flammability Rating	None
------------------------	------

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

Body Features

Primary Product Material	Silicone
Primary Product Color	Brown

Dimensions

Cavity Diameter	3.6 mm[.142 in]
Compatible Insulation Diameter Range	2.2 – 3 mm[.087 – .118 in]

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Usage Conditions

Operating Temperature (Max)	125 °C[212 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought







TE Part #963531-1
BLINDSTOPFEN




TE Part #34137
SPLICE,SOLIS, PARA, 16-14




TE Part #ANT-868-PML-UFL
Antenna R-Angle Swivel 868MHz
RG178 UFL




TE Part #2-962352-1
10P MESSERLEIS-GEH




TE Part #K1060570
Relay 29-114-12



TE Part #155880-000
CWT-11




TE Part #1393436-4
V23542C1028B300=KABELBAUMST. 8



TE Part #1393454-5
V23542C1028Z300=ABDECKK 28PDIC

TE Part #2713376002
SASR-NR504-X-15MM



TE Part #1393457-5
V23540M1000Z119=BLINDSTOPFEN (

Documents

Product Drawings
V23540M1000Z110=DICHTTULLE (F1
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1393457-4_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1393457-4_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1393457-4_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1393457-4

Single Wire Seal (SWS), Silicone, Brown, 3.6 mm [.142 in] Cavity Diameter, 2.2 – 3 mm
[.087 – .118 in] Insulation Diameter



Datasheet

English