

1-2308346-2  ACTIVE

### Rail D-Sub Backshells

TE Internal #: 1-2308346-2

Shielded, Backshell, Steel, Straight, Shell Size 5, 50 / 78 Position,  
Crimp Ferrule Termination, Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Backshells > D-SUB BACKSHELL SIZE 5



Connector Backshell Product Style: **Shielded**

Connector Backshell Product Type: **Backshell**

Primary Product Material: **Steel**

Body Orientation: **Straight**

Compatible With Connector Shell Size: **5**

[All D-SUB BACKSHELL SIZE 5 \(8\)](#)

### Features

#### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

#### Mechanical Attachment

Mating Retention Type	Jackscrew
-----------------------	-----------

Thread Size	M3
-------------	----

#### Body Features

Cable Exit Angle	180°, 45°
------------------	-----------

Primary Product Material	Steel
--------------------------	-------

#### Product Type Features

Connector Backshell Product Style	Shielded
-----------------------------------	----------

Connector Backshell Product Type	Backshell
----------------------------------	-----------

Sealable	No
----------	----

Termination Device Type	Crimp Ferrule
-------------------------	---------------

#### Housing Features

Body Orientation	Straight
------------------	----------

Compatible With Connector Shape	D-Shaped
---------------------------------	----------

#### Operation/Application

Compatible With Connector Shell Size

5

**Configuration Features**

Number of Positions

78, 50

**Usage Conditions**

Operating Temperature Range

-40 – 90 °C [-40 – 194 °F]

**Other**

EU RoHS Compliance

Compliant with Exemptions

EU ELV Compliance

Compliant

**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024  
(241)Candidate List Declared Against: JAN 2024  
(240)

SVHC &gt; Threshold:

Pb (3.5% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability


**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


**Compatible Parts**

TE Part # 1-2308348-8  
CRIMP FLANGE 8 LARGE


## Also in the Series | Rail D-Sub Backshells




Connector Contacts(5)



Connector Hardware(19)



Connector Strain Relief(67)



D-Sub Backshells &amp; Clamps(55)

## Customers Also Bought

TE Part #227161-1  
RTANG JK W/MTG PINS, BNC PCBTE Part #5536385-5  
ASSY,PIN,EUROCARD,TYPE B,LEAD-TE Part #794617-6  
6POS,MICRO MNL,RCPT HSGTE Part #9-2176390-5  
RQ 1206 11K 0.1% 10PPM 5K RLTE Part #2-2176391-1  
RQ 1206 20K 0.1% 10PPM 5K RLTE Part #2-2176390-4  
RQ 1206 2K0 0.1% 10PPM 5K RLTE Part #4-2176391-8  
RQ 1206 38K3 0.1% 10PPM 5K RLTE Part #6-2176389-5  
RQ 1206 499R 0.1% 10PPM 5K RLTE Part #3-2176391-3  
RQ 1206 26K7 0.1% 10PPM 5K RLTE Part #7-2176390-0  
RQ 1206 6K04 0.1% 10PPM 5K RL

## Documents

### Product Drawings

[FULL METAL HOODS SIZE 5 - 2 \(RAW\)](#)

English

---

### Datasheets & Catalog Pages

[Rail D-Sub Backshells Flyer](#)

English