

CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 1.6 mm, rolled, Pin, contact material: Cu alloy, nickel-plated, contact surface: silver-plated, connection cross section: 1.5 mm² ... 2.5 mm², AWG 16 ... 14

Commercial data

Item number	1004365
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	BF7AIB
Catalog page	Page 667 (C-2-2019)
GTIN	4055626472553
Weight per piece (including packing)	0.377 g
Weight per piece (excluding packing)	0.377 g
Customs tariff number	85366990
Country of origin	TR

CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Technical data

Notes

General	This product replaces 1884089 CK1,6-ER-1,50ST AG
---------	--

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Type	Individual male contact
Contact material type	rolled


Connection data

Connection method	Crimp connection
Contact connection type	Pin
Connection technology	Crimp connection
Conductor cross section	1.5 mm ² ... 2.5 mm ²
Connection cross section AWG	16 ... 14
Stripping length of the individual wire	4 mm
Conductor cross section flexible	1.5 mm ² ... 2.5 mm ²
Conductor cross section AWG	16 ... 14

Material specifications

Contact material	Cu alloy, nickel-plated
Contact surface material	silver-plated

Dimensions

Dimensional drawing	
Length	24.5 mm

Mechanical characteristics

CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Contact diameter	1.6 mm
------------------	--------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ER-2,50ST OIC AG - Crimp contact


1004365

<https://www.phoenixcontact.com/us/products/1004365>



Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com