

2214565-1

✓ ACTIVE

zQSFP+/QSFP28

TE Internal #: 2214565-1

zQSFP+, Cage Assembly with Integrated Connector, .8mm [.032in]

Centerline, Sealable, Signal, Operating Temperature Range -55 –

105 °C [-67 – 221 °F]

[View on TE.com >](#)

Connectors > Pluggable I/O Connectors & Cages

Form Factor: **zQSFP+**Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**Centerline (Pitch): **.8 mm [.032 in]**Sealable: **Yes**Circuit Application: **Signal**

Features

Industry Standards

UL Flammability Rating

UL 94V-0

Termination Features

Termination Method to PCB

Through Hole - Press-Fit

Termination Post & Tail Length

2 mm[.079 in]

Dimensions

PCB Thickness (Recommended)

1.57 mm[.062 in]

Contact Features

Contact Current Rating (Max)

.5 A

Contact Underplating Material

Tin

Contact Mating Area Plating Material

Gold

PCB Contact Termination Area Plating Material

Gold

Contact Mating Area Plating Material Thickness

.76 µm[30 µin]

Packaging Features

Packaging Method

Box & Tray

Configuration Features

Number of Rear EONs per Port Column

3

Number of Positions

190

Number of Ports	6
-----------------	---

Port Matrix Configuration	2 x 3
---------------------------	-------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Heat Sink Compatible	No
Circuit Application	Signal

Housing Features

Cage Material	Nickel Silver
Centerline (Pitch)	.8 mm[.032 in]

Product Type Features

Cage Type	Stacked
Form Factor	zQSFP+
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	Yes

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1551920-2
zQSFP+ connector assembly



TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP

Also in the Series | [zQSFP+/QSFP28](#)

Pluggable I/O Cable Assemblies(78)



Pluggable IO Connectors & Cages(424)



QSFP, QSFP+ & zQSFP+(424)


Customers Also Bought



TE Part #6-104069-7
100 sys 50 hdr drra shrd sn



TE Part #1-1469492-9
MULTIGIG RT 9MM GUIDE/ESD UNKE



TE Part #1-1586041-4
14P VAL-U-LOK R/A HDR V2



TE Part #1546307-4
4P .374" DR BARRIER,W/WASHER



TE Part #5-2176362-6
RQ 0402 150R 0.1% 10PPM 5K RL



TE Part #174520-1
4P CMNL PIN HDR ASSY V



TE Part #382811-2
SHUNT, ECON, PHBR15 AU, BLUE



TE Part #382811-6
SHUNT, ECON, PHBR 15 AU, BLACK



TE Part #0004-058-100L
CONT PIN



TE Part #2302794-1
RAPLUGASSY,CENTERP0,RTM,VPX,
MGRT3

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2214565-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2214565-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2214565-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[QSFP28/56 and zQSFP+ Interconnects](#)

English

Product Specifications

Product Specification

English