



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Gold**
Contact Retention Within Housing: **Without**
Contact Size: **Size 20**

Features

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	2000

Contact Features

Contact Underplating Material	Nickel
Contact Orientation	Straight
Mating Pin Diameter	1.02 mm[.04 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Thickness	.25 µm[10 µin]
Contact Mating Area Plating Material Thickness	.25 µm[10 µin]
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold



Contact Retention Within Housing	Without
Contact Size	Size 20
Contact Base Material	Copper
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Dimensions

Wire Size	24 – 20 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1643917-1
703-14-00100



TE Part # 601967-2
POSITIONER M22520/1-02


Also in the Series | ELCON Drawer




Board-to-Board Headers & Receptacles(25)



Connector Contacts(34)



Connector Hardware(1)



PCB Headers & Receptacles(25)



Power Contacts(34)



Rectangular Power Connectors(2)

Customers Also Bought



TE Part #1648110-1
[221-0010-01100=SA CONN,PIN](#)



TE Part #1650589-1
[903-19-02113=SCREW,SHOULDER,M4](#)



TE Part #1766193-1
[CONTACT,PIN,SIZE #12](#)



TE Part #6648318-1
[CONTACT,SKT,#12](#)



TE Part #1648552-1
[295-0049-01100](#)



TE Part #1650162-2
[701-65-02109=CONTACT,PIN,#20](#)




TE Part #1648111-1
[221-0011-01100](#)



TE Part #1766274-1
[CONTACT,PIN,#0](#)



TE Part #1643917-1
[703-14-00100](#)



TE Part #1643784-1
[291-0171-00100B=TA CONN,PIN](#)

Documents

Product Drawings

[701-14-02109=CONTACT,PIN,#20](#)

English

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_1650155-1_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1650155-1_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1650155-1_Y.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

AMP & ELCON Power Connector Layout Forms Datasheet 6-1773444-7

English

Product Specifications

Application Specification

English