



TE Internal #: 5227161-7
BNC Connector, Jack, 50 ohm, Bayonet, 4 GHz, Cable-to-Board, 1
Position, Printed Circuit Board, Panel Mount, -55 – 85 °C [-67 – 185 °
F], Zinc, Nickel
[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors > BNC RF Connector: Male (Jack), Right Angle



RF Interface: **BNC**
RF Connector Style: **Jack**
RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Bayonet**

[All BNC RF Connector: Male \(Jack\), Right Angle \(31\)](#)

Features

Housing Features

Housing Color	White
---------------	-------

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	4.11 mm[.162 in]

Packaging Features

Packaging Quantity	35
Packaging Method	Tube, Box & Tube

Other

Grade	Commercial
Dielectric Material	Polymethylpentene
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Contact Features



RF Connector Center Contact Underplating Material	Nickel
	30 µin
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Mechanical Attachment

Panel Attachment Style	Rear Mount
PCB Mount Retention	With
Panel Mount Feature Type	Lockwasher and Nut
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Solder
Detent	With

Electrical Characteristics

EMI & RFI Protection & Suppression Type	PCB Ground
Impedance	50 Ω

Dimensions

Mounting Post Length	3.48 mm[.137 in]
Profile Height from PCB	13.18 mm[.519 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board



Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Body Features

Body Material	Zinc
Body Plating Material	Nickel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-5227079-1
COMM BNC PLUG



TE Part # 5330876
BNC PLUG



TE Part # 5413771-3
JACK BLKHD,COML BNC,HEX CRIMP



TE Part # 5227079-7
COMM. BNC-PLUG



TE Part # CAT-076-BNCJKISG50
BNC RF Connector: Jack Assembly, Isolated Ground Protection, 50 Ohm



TE Part # CAT-076-BNCJKSH50
BNC RF Connector: jack assembly - short, 50 Ohm, 4Ghz



TE Part # 5227079-6
COMM. BNC-PLUG



TE Part # 5227169-5
BNC - SOLDER RECEPT



TE Part # 5227169-8
BNC - SOLDER RECEPT



TE Part # 5228980-7
JACK,BHD,COML,SERIES BNC,GOLD



TE Part # 5227079-5
COMM BNC PLUG



TE Part # 5227169-7
BNC SOLDER JACK RECEPTACLE



TE Part # 1-329631-2
JAM NUT, PLATED



TE Part # 1-5221128-0
PLUG,COMMERCIAL BNC



TE Part # 1-5227079-6
COMM BNC PLUG



TE Part # 5413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 5228979-7
JACK,COML,SERIES BNC,GOLD PL



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 1-5221128-7
PLUG,COMMERCIAL BNC

Customers Also Bought



TE Part #5-1624113-7
3650 0805 0.33uH 5% 2K RL

TE Part #5787973-1
36 .8MM CHAMP RCPT ASSY

TE Part #1-1623774-3
C14 100K 5% (LOOSE)

TE Part #ANT-W63-MON-RPS
Antenna MON Wifi6/6E Swivel SMA

TE Part #1-2176507-2
CJP 200W 4R7 5% Lead

TE Part #4-2176369-7
RQ 0603 121R 0.1% 10PPM 5K RL

TE Part #1-2176155-8
TLM 0805 0.25W R015 1% 100PPM 5K RL

TE Part #6-1879499-5
CRGH2010 5% 470R 1W

TE Part #969030-1
JUN-POW-TIM KONAKT

TE Part #6-2176369-5
RQ 0603 187R 0.1% 10PPM 5K RL

Documents

Product Drawings

RTANG JACK W/MTG PINS, BNC PCB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5227161-7_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5227161-7_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5227161-7_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



BNC Connectors

English

Product Specifications

Product Specification

English

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English