




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Dimensions

Connector Width	7.62 mm[.3 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	13.97 mm[.55 in]
Connector Length	13.97 mm[.55 in]
Profile Height from PCB	14.73 mm[.58 in]

Packaging Features

Packaging Quantity	200
Packaging Method	Bag

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions



Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	2.2 mm[.087 in]
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
Contact Size	2.2mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Shape & Form	Round
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Pin
Contact Current Rating (Max)	12 A

Housing Features

Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]



Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Number of Power Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	White
-----------------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)



Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1586174-1 06P UMNL PIN HDR 94VO NDH	 TE Part # 1586170-1 15P UMNL PIN HDR 94VO NDH	 TE Part # 1-1703062-2 CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK	 TE Part # 2029397-1 03P UMNL PIN HDR ASY 94VO NODH
 TE Part # 1586076-1 02P UMNL PIN HDR W/O DRNS V2	 TE Part # 1-641964-1 02P UMNL HDR ASSY POL BLK	 TE Part # 1-350778-9 02P UMNL V0 CAP HSG BLACK	 TE Part # 1-350778-2 02P UMNL V0 CAP HSG RED
 TE Part # 1-480699-6 02P UMNL CAP HSG BLU	 TE Part # 794584-2 05P UMNL SOC HDR ASS POL BLACK	 TE Part # 794876-1 02P UMNL PIN HDR ASSY POL 94VO	 TE Part # 1586077-1 03P UMNL PIN HDR ASSY W/O DRNS





TE Part # 1586134-1
05P UMNL PIN HDR V2 NATL NDH



TE Part # 643250-1
02P UMNL ASSY MOD HSG V0



TE Part # 643408-3
06P UMNL PIN HDR ASY POL V0 AU



TE Part # 1-480699-5
02P UMNL CAP HSG GRN



TE Part # 1-480699-8
02P UMNL CAP HSG GRY



TE Part # 1-480699-0
02P UMNL CAP HSG NATL



TE Part # 1586162-1
03P UMNL PIN HDR 94VO NDH



TE Part # 794878-1
03P UMNL PIN HDR ASSY 94VO

Also in the Series | Universal MATE-N-LOK



Connector Caps & Covers(34)



Connector Contacts(209)




Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)




Insertion & Extraction Tools(4)



PCB Headers & Receptacles(284)



Power Contacts(209)




Wire-to-Board Headers & Receptacles (284)

Customers Also Bought



TE Part #3-647609-5
05P MTA100 HDR ASSY F/L LF



TE Part #1586042-4
4P VAL-U-LOK R/A HDR V0



TE Part #7-1393239-7
RT314A03



TE Part #643749-1
06P UMNL HDR ASSY W/O DRNS





TE Part #1630880-4
FSQ5 R47 5%



TE Part #487378-6
007 HOUSING FFC RCPT 100CL SR



TE Part #1-1721261-3
OJ-SH-112LMH2.000T0



TE Part #1-1721539-7
OJE-SS-112HM2.000T0

TE Part #1-1461116-8
OJT-SH-124DM,000T0



TE Part #1969498-1
ASSY, TAB HDR, 7MM, 6.35 SERIES, 2 POS

Documents

Product Drawings

02P UMNL HDR 94VO NDH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1586161-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1586161-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1586161-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English