



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: **No Thermal Protection, Not Optic Compatible, Zhaga Inspired**

Operating Voltage: **60 VDC**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Component**

Number of Positions: **2**

Features

Housing Features

Housing Material	PBT GF
------------------	--------

Operation/Application

Circuit Application	Power
---------------------	-------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	3 A

Product Type Features

COB Substrate Thickness	1 mm
LED Holders Product Type	LED Holder
Connector System	Wire-to-Component
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

--	--



Current Rating (Max)	3 A
Operating Voltage	60 VDC

Configuration Features

Lighting Connector Features Included	No Thermal Protection, Not Optic Compatible, Zhaga Inspired
Number of Positions	2

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213678-5
Z35 MINI LED HOLDER 13.5*13.5MM
PANHEAD

Also in the Series | LUMAWISE LED Holders

LED Holders(70)

Customers Also Bought

<div></div> <div>TE Part #2213480-1 LUMAWISE Z50 HOLDER 2828 GENERAL</div>	<div></div> <div>TE Part #2213382-1 LUMAWISE LED HOLDER Z50 LOW PROFILE 1619</div>	<div></div> <div>TE Part #1-2834049-1 REC MOD, 2P LATCHED POKE-IN WTW CONN.NL</div>	<div></div> <div>TE Part #2834048-1 PLUG, 2P LATCHED POKE-IN WTW CONN.NL</div>
<div></div> <div>TE Part #1625856-6 RH73 2A 40M 10% 100PPM 1K RL</div>	<div></div> <div>TE Part #CAT-C8114-M8794 MRI LED Lighting Filters, Corcom</div>	<div></div> <div>TE Part #6-1609128-4 3FB3-MS=F8440</div>	<div></div> <div>TE Part #2058943-2 Cable Assembly Mini CT 3 pos.</div>

Documents

CAD Files



3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213678-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213678-6_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213678-6_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE LED Holder Type Z35

English

LUMAWISE LED Holder Type Z35

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

KEMA Certificate label

English