



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Opener**

Insertion & Extraction Tool Application: **Contact-to-Wire**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Product Type Features

Insertion & Extraction Tool Type	Opener
Insertion & Extraction Tool Application	Contact-to-Wire

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-2271454-6
D3950 REC 6POS 1ROW X KEY WITH MARKING



TE Part # 2271454-6
D3950 REC 6POS 1ROW X KEY



TE Part # 1-2349815-2
D3950 REC 8POSN. 1ROW X KEY MARKED

Also in the Series | Dynamic 3000 Series




Connector Contacts(94)




Connector Hardware(8)



Insertion & Extraction Tools(2)




PCB Headers & Receptacles(282)



PCB Terminal Blocks(37)




Power Contacts(94)




Wire-to-Board Headers & Receptacles (282)

Customers Also Bought






TE Part #1-5177986-3
0.8FH,P06H.5,080,08/Sn,TR,SC



TE Part #2-5177986-4
0.8FH,P07H.5,100,08/Sn,TR,SC



TE Part #5084616-4
0.8FH,R13H.5,100,08/Sn,TR,SC



TE Part #1-2271457-8
D3950 HDR 8POS 1ROW X KEY




TE Part #6-2260663-1
DYNAMIC D5900 REC CONNECTOR
ASSY 6P-X




TE Part #42233-7
205 FASTON REC 18-14 AWG TPBZ




TE Part #1-1649328-3
RT314012



TE Part #2260828-1
DYNAMIC D5900 OPENER



TE Part #2305218-1
MICRO STACK HDR ASSY 6.75MM 0.1
GOLD



TE Part #1871186-3
1.5VP REMODEL AND 1.0VP CABLE
ASSY

Documents

Product Drawings
DYNAMIC D3900 SPRING OPENER

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1981045-1_C.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1981045-1_C.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1981045-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DYNAMIC SPRING CLAMP SERIES

English

DYNAMIC SPRING CLAMP SERIES

Japanese

1-1773721-5_DYNAMIC_SERIES_QRG

English

Product Specifications

Product Specification

Japanese

Product Specification

English

Product Specification

English