




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Guide Socket Module**

Primary Product Material: **Zinc Alloy**

Hardware Accessory Function: **Guide Hardware**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Industry Standards

Industry Standard	VITA 41
-------------------	---------

Configuration Features

Key Orientation	315°
-----------------	------

Mechanical Attachment

Product Plating Finish	Chromate Conversion Coating
------------------------	-----------------------------

Dimensions

Product Length	22.5 mm[.886 in]
----------------	------------------

Packaging Features

Packaging Method	Package
Packaging Quantity	250

Body Features

Product Orientation	Right Angle
Primary Product Material	Zinc Alloy

Product Type Features

Connector Hardware Accessory Type	Guide Socket Module
Hardware Accessory Function	Guide Hardware

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1410963-8
VITA 41 KEYED GUIDE PIN



Customers Also Bought



TE Part #6368035-4
2X6 OFFSET STK MJ,SHLD,G/Y
LED&GND



TE Part #1888653-5
2X1 OFFSET ST/JK WITH LEDS




TE Part #5-104809-4
05 MTE HDR SRST LATCH W/HLDWN




TE Part #17-015A
15PSIA BOARD MOUNT PRESSURE
SENSOR




TE Part #1871058-3
PCI EXPRESS CONN. EON TYPE, 98



TE Part #1871916-1
SD RVS 0H EMBOSS ASSY



TE Part #1982995-3
CROWN CLIP JUNIOR SCREW-
MOUNT CONN



TE Part #5-2232546-1
GI2.5 HDR ASS 5P NC NO BOSS TAPE



TE Part #2305234-1
SOCKET P HARDWARE DUST COVER



TE Part #3-1469373-7
ATCA GUIDE MODULE RA FEMALE

Documents

Product Drawings

VITA 41 KEYED GUIDE MODULE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1410465-8_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1410465-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1410465-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

- Product Specifications
- Application Specification

English