




TE Internal #: 2-966067-1
Ferrule, 11 AWG, 4 mm² Wire, 8234 CMA, Closed Barrel, Tin
Plating, Length 26 mm [1.024 in], Bag, Discrete Wire, Stranded
Wire, Partially Insulated
[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: **Ferrule**
Compatible Insulation Diameter Range: 4.7 mm [.185 in]
Wire Size: **8234 CMA**

Features

Body Features

Primary Product Color	Gray
-----------------------	------

Product Type Features

Sealable	No
Compatible With Discrete Wire Type	Stranded

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Dimensions

Strip Length	20 mm[.787 in]
2-Wire Size	11 AWG
Compatible Insulation Diameter Range	4.7 mm[.185 in]
Wire Size	8234 CMA
Barrel Inside Diameter	4.8 mm[.19 in]
Terminal Material Thickness	.2 mm[.007 in]
Overall Product Length	26 mm[1.024 in]

Contact Features



Contact Mating Area Length	18 mm[.702 in]
Crimp Wire Terminal Type	Ferrule
Barrel Type	Closed
Terminal Plating Material	Tin
Terminal Orientation	Straight

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2-1579001-3
CSE10-AE22 CRIMP HEAD




TE Part # 539660-1
ADERENDHUELSEN (Ferrule) Crimp Tool


Customers Also Bought




TE Part #T4131512041-000
M12,REAR MOUNT,FEMALE,D,4P, SOLDER WIRE




TE Part #5-1415899-5
RZ03-1C3-D024




TE Part #2-966067-7
FER,WIRE,PL SLV,16.00/6,L18,BLUE,LP




TE Part #282847-2
TERMI-BLOK PCB MOUNT 35 2P.5




TE Part #284041-2
TERMINAL BLOCK VERTICAL PLUG S




TE Part #2-966067-5
FER,WIRE,PL SLV,10.00/8,L18,RED,LP




TE Part #281739-8
HEADER HE14 STRAIGHT 2X8 P



TE Part #YDTS24W09-35SAV001
RECP ASSY



TE Part #CTD160E01F
MODULE ASSY



TE Part #449582-000
VERSAFIT-MINI-SPL-3/4-BK

Documents

Product Drawings
FER,WIRE,PL SLV,4.00/12,L18,GREY,LP
English



CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-966067-1_B1.2d_dxf.zip

English

Customer View Model

ENG_CVM_2-966067-1_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_2-966067-1_B1.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-966067-1_B1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-966067-1_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-966067-1_B1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wire Ferrules

English

WIRE END FERRULES

English

Agency Approvals

CSA Certificate

English