



Connectors > PCB Connectors > PCB Headers & Receptacles > SUPERSEAL Connector Headers: 1.0 mm



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board, Wire-to-Device**

Number of Positions: **26**

Number of Rows: **4**

[All SUPERSEAL Connector Headers: 1.0 mm \(35\)](#)

Features

Industry Standards

IP Rating	IPX7
-----------	------

Electrical Characteristics

Operating Voltage	250 VDC
Voltage Rating (Max)	250 VDC
Nominal Voltage Architecture	24 V, 240 V, 42 V, 12 V, 48 V

Dimensions

Connector Width	39 mm[1.53 in]
Profile Height from PCB	24.7 mm[.972 in]
Connector Length	36.5 mm[1.44 in]

Packaging Features

Packaging Quantity	17
Packaging Method	Tube



Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Body Features

Connector & Keying Code	2
Primary Product Color	Black

Operation/Application

Shielded	No
Circuit Application	Signal

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
Mounting Holes	With
Mating Retention	With
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Contact Features

Mating Pin Diameter	1 mm[.039 in]
Contact Size	1mm
Contact Mating Area Plating Material	Gold
Contact Type	Pin

Configuration Features

Number of Signal Positions	26
Number of Sections	1
PCB Mount Orientation	Vertical
Number of Positions	26
Number of Rows	4

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular



PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board, Wire-to-Device
Header Type	Fully Shrouded
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Housing Features

Centerline (Pitch)	3 mm[.118 in]
--------------------	---------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-SU763-CH8172
SUPERSEAL Connector Housings: 1.0 mm

Also in the Series | SUPERSEAL 1.0mm

Automotive Headers(39)

Automotive Housings(20)

Automotive Terminals(10)

Rectangular Backshells & Clamps(3)

Customers Also Bought

TE Part #3-2176058-1
RLP73K 3A R18 5% 2K RL

TE Part #4-1879071-5
THS50 330R 5%

TE Part #5745653-2
DIECAST STRAIN RELIEF KIT, SZ 3


TE Part #1-2176085-3
EP 9W (S) 1K0 5%

TE Part #1-1624322-1
UPW25 0.1% 5PPM 350R

TE Part #6-1676913-0
YR1 0.1% 274R

TE Part #5-1676914-8
YR1 0.1% 549R

TE Part #9-2176312-1
RP 1E 0.1W 107K 0.1% 25PPM 1K RL



Documents

Product Drawings

SUPER SEAL 26POS CAP ASSY V AU

Japanese

SUPER SEAL 26POS CAP ASSY V AU

Japanese

CAD Files

Customer View Model

ENG_CVM_CVM_6473418-1_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6473418-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6473418-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Receptacle Contact, Super Seal Connector

Japanese

Application Specification

Japanese

Super Seal Connector

Japanese

Application Specification

Japanese



Instruction Sheets

Instruction Sheet (non U.S.)

English

SUPER SEAL CONNECTOR PLUG HOUSING CONNECTOR

English

Agency Approvals

UL Report

English