

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-24-207629	16MAY2024	SA	DSC


AMP WIRE RANGE
22-16 AWG STRANDED

1 WIRE INSULATION DIA .080 TO .125.

2 FINISH: BODY AND SLEEVE:
TIN PLATE PER ASTM B545.

3 MATERIAL: BODY AND SLEEVE,
COPPER PER ASTM B152
INSULATION: PVF²
COLOR- NATURAL

4 MARKING 22-18 FOR MILITARY;
COMMERCIAL RANGE 22-16



1000	LOOSE PIECE	696427-1
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C		THIS DRAWING IS A CONTROLLED DOCUMENT.		 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: —	DIMENSIONS: INCHES 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .008 3 PLC ± — 4 PLC ± — ANGLES ± —	NAME SPLICE, BUTT, PVF2 , P.I.D.G., WIRE SIZE: 22-16 AWG				
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111				CIRCULAR MIL AREA: 0.26-1.65mm² [509-3,260] STRANDED	APVD T MICHIELUTTI 19AUG05	PRODUCT SPEC —	APPLICATION SPEC —	
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 	FINISH 	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-696427	RESTRICTED TO —
CUSTOMER DRAWING							SCALE 1:1	SHEET 1 OF 1	REV B	