




TE Internal #: 1437259-6  
C-Clip PCB Spring Contact, Uncompressed Height 4 mm [.157 in],  
Length 7 mm [.276 in], Width 2.5 mm [.098 in], 2.6 mm [.102 in]  
Working Range (Low)  
[View on TE.com >](#)

Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **C-Clip**  
Scalable: **No**  
Side Protected: **No**  
Uncompressed Height: **4 mm [.157 in]**  
Product Length: **7 mm [.276 in]**

Features

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	2000

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	2.6 mm[.102 in]
Contact Working Range (High)	3.5 mm[.138 in]
Point of Contact Area Plating Material	Gold
Contact Current Rating (Max)	1.5 A

Configuration Features

Number of Positions	1
Side Protected	No

Product Type Features

--	--



Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	C-Clip
Scalable	No

Dimensions

Uncompressed Height	4 mm[.157 in]
Product Length	7 mm[.276 in]
Product Width	2.5 mm[.098 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 3-2199250-4  
TYPE C 3.6H SPRING FINGER




TE Part # 2343297-2  
SPRING FINGER



TE Part # 1734303-1  
SHIELD FINGER 4025B-T

Customers Also Bought




TE Part #5177983-6  
0.8FH,R05H.5,140,08/Sn,TU



TE Part #8-1415537-0  
SR6B6K24



TE Part #1393236-2  
V23092-A1005-A301



TE Part #390111-1  
SKT,SODIMM,144P,SGRAM3.3V,HIGH, TY-S



TE Part #1746142-1  
LEAF TYPE BATTERY CONN 3P



TE Part #2286211-3  
HIGH CURRENT SPRING FINGER



TE Part #4-1879134-3  
RN 0603 27K4 0.1% 10PPM 1K RL



TE Part #1-2317658-0  
AV25 SPL 3A MOVING RING POWER BLUE 24V



TE Part #5-146132-2  
04 MODII HDR SR SFMNT B/A .100



TE Part #2367196-3  
1.0mm WTB RIGHT ANGLE TYPE WITH LATCH

Documents

Product Drawings  
3100089=SHIELD FINGER

English

CAD Files  
3D PDF



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1437259-6\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1437259-6\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1437259-6\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Mobile Equipment](#)

English

Product Specifications

[SHIELD FINGER 4025](#)

English

[Product Specification](#)

English