




PIDG

TE Internal #: 130114

Closed Ring Tongue Terminal, 16 – 14 AWG, M6 Stud, 6.35 mm [.25 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 2050 – 5180 CMA

Stud Size: M6

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Insulation Sleeve Color	Blue
Stripe Color	Blue

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

--	--



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	6.35 mm [.25 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	27.51 mm [1.083 in]
Compatible Insulation Diameter (Max)	3.8 mm [.15 in]
Compatible Insulation Diameter Range	2.7 – 3.8 mm [.106 – .15 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 47387  
DAHT PG PIDG 20-14 ASSY




TE Part # 169404  
CERTI-LOK DIE



TE Part # 59824-1  
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY




TE Part # 58423-1  
DIE, RBY IS9252




TE Part # 58433-3  
PRO CR ASSY, RBY IS9252


Also in the Series | PIDG




Compression Connectors(17)




Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)




Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)




Splices(41)

Customers Also Bought



TE Part #52928  
PIDG SPRSPD 22-16COM22-18MIL 5



TE Part #52420-1  
TERMINAL,PIDG SPR SPD 16-14 6



TE Part #1-1622825-0  
RL73K 3A R12 5% 1K Reel



TE Part #2430148-1  
Conn G FNG 0.8mm D-Sub 15 Pin



TE Part #3-1676123-1  
1/2W SM M/OX 5% 15R



TE Part #1622516-1  
LR1 1% 560K




TE Part #1-1414632-0  
V23132B2002X025



TE Part #2323802-8  
SSRMP-240D16R = Mini Puck,16A, 240V AC,R



TE Part #1337775-3  
75 OHM COAX BNC STR PLUG-P99-E



TE Part #554043-2  
STDOFF, MTG STUD, HEX HD

Documents



Product Drawings  
PIDG RING TONGUE

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_130114\_L.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_130114\_L.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_130114\_L.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.