

201413-4

✓ ACTIVE


AMP

TE Internal #: 201413-4

Male Screwlock, Stainless Steel / Zinc Alloy

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Hardware

Connector Hardware Accessory Type: **Male Screwlock**Primary Product Material: **Zinc Alloy, Stainless Steel**Operating Temperature (Max): **150 °C [302 °F]**Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**Hardware Accessory Function: **Latching, Locking & Retention**

Features

Mechanical Attachment

Hardware Type Included	Jackscrew Tip Male and Spirol Pin
Thread Size	6-32
Product Plating Finish	Chromate

Dimensions

Product Width	7.92 mm[.312 in]
Product Length	58.04 mm[2.285 in]
Product Height	7.92 mm[.312 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Type Features

Connector Hardware Accessory Type	Male Screwlock
Hardware Accessory Function	Latching, Locking & Retention

Body Features

Primary Product Material	Zinc Alloy, Stainless Steel
--------------------------	-----------------------------

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

JACKSCREW ASSY. SERIES "M"

English

CAD Files

Customer View Model

[ENG_CVM_CVM_201413-4_J.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model[ENG_CVM_CVM_201413-4_J.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_201413-4_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets[Instruction Sheet \(U.S.\)](#)

English

[AMP Jack Screw Selection Chart for Series "M", COAXICON and Miniature](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS](#)

English