




Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 14

Connector Product Type: Housing

Operating Voltage: 250 VDC

Wire Size: .2 – 2 mm²

Features

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling
Mating Alignment	With
Thread Size	1 1/4-18 UNEF-2A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Polyamide
Circular Connector Shell Size	20



Configuration Features

Reverse Numbering	Without
Number of Positions	14
Number of Power Positions	0
Number of Signal Positions	14

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Dimensions

Wire Size	.2 – 2 mm ²
Assembly Length	30.73 mm[1.21 in]

Contact Features

Reverse Gender	Yes
Contact Type	Socket
Contact Current Rating (Max)	13 A
Contact Protection	With

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

--	--



UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | AMP CPC



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)




Power Contacts(6)

Customers Also Bought



TE Part #2-1623732-4
BCHE 7 W 270R 5%



TE Part #207299-3
FLANGE PLUG MOUNT CPC




TE Part #206434-1
CPC PLUG ASSEMBLY SIZE 11-8



TE Part #350551-3
UMNL SOK 20-14 PTPPHBZ L/P



TE Part #1-480351-0
01P CMNL CAP HSG NATL




TE Part #213570-1
CPC RECPT 20-14 SPECIAL



TE Part #4-1393249-2
W58-XC4C12A-2=W58



TE Part #66602-6
III+ PIN,18-14,TIN-LEAD,SMPACK



TE Part #213651-1
CPC RCPT 20-14 STD SEX



TE Part #B4505CS
WHIP,MC,CC,450-470MHZ, TUN,5,CH, GP,SPRIN



Documents

Product Drawings

CPC 20-14 FREE HANGING RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_213650-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_213650-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_213650-1_K.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_213650-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_213650-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_213650-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English