

RC-0000000WQ00 - Panel mounting base



1593021

<https://www.phoenixcontact.com/us/products/1593021>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel mounting base, series: RC, straight, Screw locking mechanism, M23, Radial O-ring, 4x Ø 2.7 mm, shielded: yes, panel thickness min.: 3 mm

Commercial data

Item number	1593021
Packing unit	40 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFP
GTIN	4046356193832
Weight per piece (including packing)	25.622 g
Weight per piece (excluding packing)	23.2 g
Customs tariff number	85366990
Country of origin	DE

RC-0000000WQ00 - Panel mounting base



1593021


<https://www.phoenixcontact.com/us/products/1593021>

Technical data

Product properties

Product type	Panel mounting base
Series	RC
Application	Signal
Shielded	yes
Thread type	M23

Dimensions

Dimensional drawing	
Panel thickness	> 3 mm

Material specifications

Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Gasket and O-ring material	FPM

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

Mounting

Mounting	4x Ø 2.7 mm
----------	-------------


RC-0000000WQ00 - Panel mounting base



1593021

<https://www.phoenixcontact.com/us/products/1593021>

Drawings



Installation dimensions

RC-0000000WQ00 - Panel mounting base



1593021

<https://www.phoenixcontact.com/us/products/1593021>

Classifications

ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

RC-0000000WQ00 - Panel mounting base



1593021
<https://www.phoenixcontact.com/us/products/1593021>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com