




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Thermoplastic**

Primary Product Color: **Gray**

Compatible With Connector Shell Size: **1**

Shielded: **Yes**

Features

Dimensions

Compatible Insulation Diameter Range	4 – 8 mm[.158 – .315 in]
--------------------------------------	--------------------------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Body Features

Primary Product Plating Material	Nickel over Copper
Cable Exit Angle	37.5°
Primary Product Material	Thermoplastic
Primary Product Color	Gray

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Operation/Application

Compatible With Connector Shell Size	1
Shielded	Yes

Configuration Features

Number of Positions	9
---------------------	---

Mechanical Attachment

Thread Size	14702
-------------	-------



Packaging Features

Packaging Method	Tray, Box & Tray
Packaging Quantity	25

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Perfluorobutane sulfonic acid (PFBS) and its salts (.16% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1393738-0
[V42254A6000K109=SUB D GEHAEUSE](#)

Customers Also Bought



TE Part #2-1623728-1
[BCHE 11 W 470R 5%](#)



TE Part #1986280-1
[Receptacle Kit and Cover ODVA Ethernet](#)



TE Part #927852-8
[PL 250 REC TERMINAL 20-17 AWG SILPPB](#)



TE Part #2-1393561-9
[V42254A 262V 19=SUB D SCHRAUBE](#)



TE Part #F26778-000
[ST58-5-00](#)



TE Part #1-2134249-0
[D3900 SPRING CLAMP REC 10P w /oSEAL-typeA](#)



TE Part #3-1768017-0
[EET-0517P-4](#)



TE Part #9-1768017-7
[EET-0825P-4](#)



TE Part #4-1618394-1
[EV200BAANA=CONTACTOR, SPST-NC 12V COIL](#)



TE Part #8B-0091-001-000
[723 HTEC METAL PROTECTION CAP, EXTENSION](#)

Documents

Product Drawings

[V42254A6000G109=SUB D GEHAEUSE](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_1393738-1_B.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1393738-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393738-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[mounting guideline for d-Sub housings](#)

English

[Instruction Sheet \(U.S.\)](#)

English