

211010-4

✓ ACTIVE

AMPLIMITE

TE Internal #: 211010-4

Connector Saver, Straight, 15 Position

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Adapters & Connector Savers

Connector Interface Adapter Type: **Connector Saver**Body Orientation: **Straight**Number of Positions: **15**Centerline (Pitch): **2.29 mm [.09 in]**Contact Current Rating (Max): **5 A****Features****Body Features**

Body Plating Material	Gold
Body Material	Brass

Operation/Application

Compatible With Connector Shell Size	1
Circuit Application	Signal

Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Beryllium Copper
Contact Size	Size 22
Contact Current Rating (Max)	5 A

Product Type Features

Connector Interface Adapter Type	Connector Saver
----------------------------------	-----------------

Housing Features

Body Orientation	Straight
Centerline (Pitch)	2.29 mm [.09 in]

Configuration Features

Number of Positions	15
---------------------	----

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Usage Conditions

Operating Temperature Range	-67 – 257 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (4% in Contact/Component) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_211010-4_AU.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_211010-4_AU.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_211010-4_AU.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.