



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 52600 – 83700 CMA

Stud Size: #10

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Box

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Barrel Type	Closed
-------------	--------



Terminal Orientation	Flag
Terminal Plating Material	Tin

Dimensions

Wire Size	52600 – 83700 CMA
Stud Diameter	9.07 mm[.375 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	36.5 mm[1.437 in]
Barrel Inside Diameter	9.07 mm[.357 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1752681-3
HYP10 SOLIS FLAG 6-2AWG
INDENTER




TE Part # 1752680-5
HYP10 SOLIS FLAG 2AWG NEST




TE Part # 48510
HYP8 SOLIS FLAG 2AWG NEST


Customers Also Bought




TE Part #350209-1
02P CMNL HDR ASSY PC NATL




TE Part #350789-1
03P UMNL PIN HDR ASSY 94VO




TE Part #350786-1
02P UMNL HDR ASSY 94VO




TE Part #4-1437565-9
FSM6JSMA=SMT,TACTILE,PB SWITCH




TE Part #321059
TERMINAL,SOLIS FLAG R 4 10




TE Part #2-1676913-7
YR1 0.1% 1M0




TE Part #6-2176337-1
CRGQ 0402 1M0 1%



TE Part #T41513C9L14-002
RPC-M12L-4FS-1.0-PUR 16AWG BK



TE Part #2-2176613-5
EP 4W (SS) 10R 5%



TE Part #1462041-8
IMB03CTS=IM RELAY 140mW 5V HDV

Documents



Product Drawings

TERMINAL,SOLIS FLAG R 2 10.5MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_184147-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_184147-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_184147-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.