

RQ73C1J38K3BTD

✓ ACTIVE

Holsworthy | Holsworthy RQ73

TE Internal #: 8-2176371-9

Surface Mount Precision Resistor, Thin Film, 0603, .15 W, 38.3K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RQ73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0603**

Power Rating: **.15 W**

Resistance Value: **38.3K Ω**

Features

Industry Standards

Industry Standard	AEC-Q200 Compliant
ESD HBM Classification	0
Moisture Sensitivity Level	1

Other

Passive Component Comment	Shelf Life Based on Date of Manufacture
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	75 V
Power Rating	.15 W
Resistance Value	38.3K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Product Type Features

--	--



Shelf Life	2 Years
Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 3-2176382-0
RQ 0805 267K 0.1% 10PPM 5K RL

TE Part # 8-2176367-9
RQ 0603 38K3 0.1% 10PPM 1K RL

TE Part # 2176372-6
RQ 0603 56K2 0.1% 10PPM 5K RL

TE Part # 3-2176389-4
RQ 1206 237R 0.1% 10PPM 5K RL

TE Part # 2176371-8
RQ 0603 5K49 0.1% 10PPM 5K RL

TE Part # 4-2176391-2
RQ 1206 33K2 0.1% 10PPM 5K RL

Also in the Series | [Holsworthy RQ73](#)

Surface Mount Resistors(1954)

Customers Also Bought

RQ73C1J38K3BTD

Surface Mount Precision Resistor, Thin Film, 0603, .15 W, 38.3K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RQ73



TE Part #2000713-6
RA Keyed Guide Mod, Vita 46, Machined

TE Part #5-2301994-8
RJ45 JACK INT.MAG. 10/100 LED 1X1 INV.

TE Part #9-2176307-1
RP 1E 0.1W 107K 0.1% 25PPM 5K RL

TE Part #3-2176371-9
RQ 0603 11K5 0.1% 10PPM 5K RL

TE Part #3-1879134-9
RN 0603 24K9 0.1% 10PPM 1K RL

TE Part #8-1879134-2
RN 0603 68K1 0.1% 10PPM 1K RL

TE Part #CAT-HST-RNF3000
RNF-3000 Heat Shrink Tubing

TE Part #2102772-1
DC, 7Row, Half Left End, MULTIGIG RT 2R

TE Part #5-1879207-9
RN 0603 402K 0.1% 10PPM 5K RL

Documents

Product Drawings

RQ 0603 38K3 0.1% 10PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-2176371-9_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-2176371-9_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-2176371-9_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

RQ73C1J38K3BTD

Surface Mount Precision Resistor, Thin Film, 0603, .15 W, 38.3K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RQ73



SMD Thin Film Precision Resistors - AEC-Q200 Compliant - Type RQ73 Series

English