



1471-9 (3/13)


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2 POSITION




3 POSITION




4 POSITION



N= 5 THRU 20 POSITION



RECOMMENDED PCB LAYOUT



10.0 [1.395]	13.33[1.525]	15.0 [1.591]	2,3	5	2-2311993-5
47.5 [1.870]	50.83[2.001]	52.5 [2.067]	-	20	-
45.0 [1.772]	48.33[1.903]	50.0 [1.968]	-	19	-
42.5 [1.673]	45.83[1.804]	47.5 [1.870]	-	18	-
40.0 [1.575]	43.33[1.706]	45.0 [1.772]	-	17	-
37.5 [1.476]	40.83[1.607]	42.5 [1.673]	-	16	-
35.0 [1.378]	38.33[1.510]	40.0 [1.575]	2,4,6,8,10,12,14	15	1-2311993-5
32.5 [1.280]	35.83[1.411]	37.5 [1.476]	-	14	-
30.0 [1.181]	33.33[1.312]	35.0 [1.378]	2,4,6,8,10,12	13	1-2311993-3
27.5 [1.083]	30.83[1.214]	32.5 [1.280]	-	12	-
25.0 [1.984]	28.33[1.115]	30.0 [1.181]	2,4,6,8,10	11	1-2311993-1
22.5 [1.886]	25.83[1.016]	27.5 [1.083]	-	10	-
20.0 [1.787]	23.33[1.919]	25.0 [1.984]	2,4,6,8	9	2311993-9
17.5 [1.689]	20.83[1.820]	22.5 [1.886]	-	8	-
15.0 [1.591]	18.33[1.722]	20.0 [1.787]	2,4,6	7	2311993-7
12.5 [1.492]	15.83[1.623]	17.5 [1.689]	-	6	-
10.0 [1.395]	13.33[1.525]	15.0 [1.591]	2,4	5	2311993-5
7.5 [1.295]	10.83[1.426]	12.5 [1.492]	-	4	-
5.0 [1.197]	8.33[1.328]	10.0 [1.395]	2	3	2311993-3
2.5 [1.098]	5.83[1.229]	7.5 [1.295]	-	2	-
DIM C	DIM B	DIM A	OMIT PIN#	NO. OF POSITIONS.	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN OTTO CHEN 20DEC2016		 TE Connectivity				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK DANIEL 23JAN2017		NAME HEADER ASSEMBLY, VERTICAL, ECONOMY POWER, 2.5mm CENTERLINE -		
		APVD DANIEL 23JAN2017		PRODUCT SPEC 108-2418				
		APPLICATION SPEC 114-13315		SIZE A2				
		WEIGHT -		CAGE CODE 00779				
MATERIAL - -		FINISH - -		DRAWING NO G=2311993		RESTRICTED TO -		
CUSTOMER DRAWING						SCALE 4:1	SHEET 2 OF 2	REV A