



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 1.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Dimensions

Product Length	20.44 mm[.805 in]
Compatible Insulation Diameter Range	3.05 – 3.68 mm[.12 – .145 in]
Terminal Material Thickness	.43 mm[.017 in]
Wire Size	.82 – 1.31 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 61873-1
250 FASTON REC 18-14 AWG TPBR

TE Part # 2217483-2
KIT, BTLI, DOUBLE ACTION HEAD

TE Part # 2217483-1
KIT, BTLI, DOUBLE ACTION HEAD

TE Part # 5-160563-2
250 FASTON REC 18-16 AWG TPBR

TE Part # 42025-4
250 FASTON REC 18-16 AWG TPBR

TE Part # 90165-1
DAHT 250 FASTON REC 18-14 ASSY

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(425)



Splices(4)

Customers Also Bought



TE Part #DT06-2S-CE05
PLG, 2P, BLK, E, SEAL RET, CAP



TE Part #7-2176231-6
3522 13K 1% 3W



TE Part #9-1437624-4
PKS1103B101/4=KNOB PLSTC AL/SK




TE Part #2-2176502-1
CJP 60W 10R 5% Lead




TE Part #9-1676123-8
1/2W SM M/OX 5% 9K1




TE Part #1-2176416-0
9W STD M/OX 5% 120R




TE Part #6-487508-3
TRIOMATE ASY H14P L=3.175,LDFR



TE Part #1-480416-8
250 FASTON HSG.,REC.,1 POS, NATRUAL



TE Part #58524-2
PROCrimper DIE



TE Part #58525-2
PROCrimper DIE

Documents

Product Drawings
250 FASTON REC 18-14 AWG TPBZ
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_42025-1_AG.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_42025-1_AG.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42025-1_AG.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTIN_FASTON_Product_Line](#)

English

Product Specifications

[Engineering Report](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English