



Connectors > Connector Accessories > Connector Strain Relief > Ribbon Cable Connector: Pull Loop



Strain Relief Accessory Type: Pull Loop

Primary Product Material: PVC

Primary Product Color: Natural

Packaging Method: Box & Carton

Packaging Quantity: 250

[All Ribbon Cable Connector: Pull Loop \(10\)](#)

Features

Industry Standards

| | |
|---|-----------------------|
| Compatible With Agency/Standards Products | UL, CSA |
| Compatible With Approved Standards Products | UL E28476, CSA LR7189 |

Dimensions

| | |
|--|--------|
| | .64 in |
|--|--------|

Product Type Features

| | |
|------------------------------|-----------|
| Strain Relief Accessory Type | Pull Loop |
|------------------------------|-----------|

Body Features

| | |
|--------------------------|---------|
| Primary Product Material | PVC |
| Primary Product Color | Natural |

Packaging Features

| | |
|--------------------|--------------|
| Packaging Method | Box & Carton |
| Packaging Quantity | 250 |

Other



| | |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1658624-1
10 NOVO DUAL 30DP, LEAD FREE



TE Part # 2-111623-1
20, 2MM, POL,30 DP, LEAD FREE



TE Part # 1-111626-9
20, 2MM, 30 DP, LEAD FREE



TE Part # 1658527-5
622-1430LF FEM SOCKT,LEAD FREE





TE Part # 1658620-2
14 NOVO MIL 15DP, LEAD FREE



TE Part # 1658621-2
14 NOVO MIL/CTR 15DP,LEAD FREE

Customers Also Bought



TE Part #1658654-1
KIT,HDP-20,ENCLSUR,RCPT,SIZE 1



TE Part #499252-9
014 STRAIN RELIEF A-L RCPT



TE Part #3-770522-1
SL156 HOODED CONTACT, LP LF



TE Part #6609056-4
20MV1=F7759 S0



TE Part #34141
PG R 22-16 COMM 22-18 MIL 4



TE Part #36189
BUDG R 22-16 COMM 22-18 MIL 4



TE Part #644752-8
08P MTA156 HDR ASSY SQ STR F/L



TE Part #644752-2
02P MTA156 HDR ASSY SQ STR F/L



TE Part #2201778-1
MICRO SD PUSH PUSH LOW PROFILE TYPE



TE Part #5-146280-3
03 MODII HDR SRST B/A .100CL

Documents

Product Drawings

PULL LOOP, CUT LENGTH .64 IN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5088450-3_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5088450-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5088450-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English