




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 4

Terminal Block Connector Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Rows: 1

Wire Entry Angle: 45°

Features

Housing Features

Housing Material	High Temperature Nylon or Polyester
------------------	-------------------------------------

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Method to Wire & Cable	Push-in

Body Features

Primary Product Color	Green
Product Orientation	Vertical

Packaging Features

Packaging Method	Box & Carton
------------------	--------------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper
Contact Current Rating (Max)	5 A



Configuration Features

Wire Entry Location	Top
Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1
Wire Entry Angle	45°

Product Type Features

Terminal Block Connector Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Dimensions

Wire Size	26 – 20 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2834334-2
4.0PITCH ITB CONN_2P_W
CAP_NATURAL



TE Part # CAT-SL36-M6642B
Miniature Headers, SlimSeal



TE Part # 2834167-3
RELEASABLE SLIM CONTACT



TE Part # 2834006-1
RELEASE POKE-IN
CONNECTOR_1POLES



TE Part # 2834385-2
RELEASE POKE-IN
CONNECTOR_2P_NATURAL

Customers Also Bought



TE Part #8-6609940-7
PM0S0DS6B=C3401



TE Part #5747461-3
HD-20 RCPT 25P RA 590 THD INS



TE Part #749809-9
KIT,PLUG,25P,HDE



TE Part #1877285-3
03P EP SHRD HDR ASMY, WHITE



TE Part #8-1879512-9
CRGH0805 1% 27R 0.33W

TE Part #167296-1
50P.HDP20 PLUG ASSY

TE Part #5-104655-1
10 50/50 HDR DRST SFMNT TIN

TE Part #201595-000
SO96-2-00

TE Part #2-2176606-2
RLC73PD 3A 1R0 1% 2K RL

TE Part #2154828-2
Cable Assembly EPII 3 Pos

Documents

Product Drawings
4POS 2.5MM TES CONN.

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-2834021-4_1.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1-2834021-4_1.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-2834021-4_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
Modular Screwless Terminal Blocks Flyer (Chinese)

BUCHANAN WireMate Connectors Brochure

BUCHANAN WireMate Connectors Brochure

English

Modular Screwless Terminal Blocks Flyer

English

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English