




Switches > Slide Switches



Contact Current Rating: **.3 A**

Configuration (Pole-Throw): **Double Pole - Double Throw**

Product Orientation: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Features

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Tray
------------------	------

Dimensions

Product Width	5.8 mm[.228 in]
Product Length	14 mm[.551 in]
Actuator Length	2.3 mm[.09 in]

Other

Grade	Instrumentation
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Termination Features

Termination Post & Tail Length	3 mm[.118 in]
--------------------------------	---------------



Termination Method to PCB

Through Hole - Solder

Body Features

Actuator Orientation	Top
Actuator Travel	2 mm[.079 in]
Product Orientation	Vertical
Actuator Profile	Extended
Actuator Material	POM
Actuator Color	Black

Configuration Features

Terminals Connected	2-1, 5-4
Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Number of Positions	2
Operating Function	On On

Electrical Characteristics

Contact Current Rating	.3 A
Operating Voltage	125 VAC

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1825257-1
[MSS120004=SPDT SL SW VERT AG](#)




TE Part # 1825255-5
[MHS12304=SPDT SL SW VERT AG](#)



TE Part # 1825255-8
[MHS133G04=SP3T SL SW VERT AU](#)




TE Part # 1825255-7
[MHS13304=SP3T SL SW VERT AG](#)



TE Part # 1825258-2
[SPDT SL SW R/A AU](#)

Also in the Series | [Alcoswitch MSS](#)




[Slide Switches\(15\)](#)


Customers Also Bought



TE Part #3-1462037-1
IM42GR =IM RELAY 100mW 4.5V BIS



TE Part #5788801-1
25 HTMSFL ASSY RA 318 (SL,BL)




TE Part #1-640518-0
03P MR II PLUG HSG




TE Part #643232-1
05P UMNL HDR ASSY R/A 94VO



TE Part #1-6450160-0
MBXL R/A RCPT 2P+24S+2P




TE Part #2-215911-0
20 WAY GREY MK II RECP




TE Part #7-1437648-4
4PCV-05-006=#4 TRIBARRIER TERM



TE Part #1-1625893-0
5W SM M/OX 5% 51K



TE Part #8-1437648-0
4PCV-06-006=4PCV ASSEMBLY



TE Part #1393310-3
VCF4-1000=FROM SEC

Documents

Product Drawings

MSS220004=DPDT SL SW VERT AG

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825261-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825261-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1825261-1_A1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English