



Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Vertical Mount



Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **17 W**

Resistance Class: **1kΩ – 1MΩ**

Resistance Value: **22K Ω**

[All Wirewound Resistor: Vertical Mount \(166\)](#)

Features

Usage Conditions

Operating Temperature Range	-55 – 350 °C
Temperature Coefficient	±200 ppm/°C

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	17 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	22K Ω
Passive Component Tolerance	10 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
--------------------------------	--------



Number of Terminations	2
------------------------	---

Dimensions

Passive Component Dimensions	75 x 9 x 10 mm
------------------------------	----------------

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-C339-SB19B
[Wirewound Resistor: Vertical Mount](#)



TE Part # 1623728-3
[BCHE 11 W 10R 5%](#)

Also in the Series | [CGS SBC](#)



[Surface Mount Resistors\(1\)](#)




[Through-Hole Resistors\(212\)](#)

Customers Also Bought



TE Part #8-188275-6
[MICRO-MATCH SMD FTE](#)




TE Part #5177986-2
[0.8FH,P05H.5,060,08/Sn,TR,SC](#)



TE Part #5-1393243-2
[RT424F05](#)



TE Part #3-644466-6
[06P MTA156 CONN ASSY 20AWG YEL](#)



TE Part #5-103639-3
[04 MTE HDR SRST LATCH .100CL](#)




TE Part #350792-1
[04P UMML PIN HDR ASSY 94VO](#)




TE Part #350789-1
[03P UMNL PIN HDR ASSY 94VO](#)



TE Part #5-103639-1
[02 MTE HDR SRST LATCH .100CL](#)



TE Part #643071-6
[06P MTA156 FD-THRU COVER](#)



TE Part #9-1879140-7
[RN 0603 187K 0.1% 10PPM 5K RL](#)



Documents

Product Drawings

SBCV15 22K 10%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1623734-3_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1623734-3_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1623734-3_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

High Power Resistor - Type SBC (Square Ceramic) Series - Tyco Electronics Passives

English