

277164-1

✓ ACTIVE

COPALUM

TE Internal #: 277164-1


Butt Splice, 8 AWG, 8.8 mm² Wire, Sealable, Transitional, 16983

CMA, Copper, Length 57.4 mm [2.26 in], Box, Open Barrel,

Stranded Wire

[View on TE.com >](#)

Terminals & Splices > Splices > COPALUM Sealed: Butt Splices

Splice Type: **Butt Splice**Wire Size: **8.8 mm²**Sealable: **Yes**Splice Features: **Transitional**[All COPALUM Sealed: Butt Splices \(11\)](#)**Features****Packaging Features**

Packaging Quantity 25

Packaging Method Box

Contact Features

100 µin

Terminal Plating Material Nickel

Contact Base Material Copper

Barrel Type Open

Body Features

Product Weight 30.923 g

Splice Features Transitional

Product Type Features

Splice Accessory Type Splice

Splice Type Butt Splice

Sealable Yes

Compatible With Discrete Wire Type Stranded

Configuration Features

Compatible With Wire & Cable Type Discrete Wire

Dimensions

Wire Size	16983 CMA
Compatible Insulation Diameter Range	7.37 mm [.29 in]
Terminal Material Thickness	2.41 mm [.095 in]
Product Length	57.4 mm [2.26 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 175 °C [-85 – 347 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on'

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 68008-1
DIE ASSY #4 SEALED COPALUM



TE Part # 1490557-1
HYP10 COPALUM SEALED 4AWG DIE SET

Customers Also Bought



TE Part #328860
WIRE CAP,TFL .088-110



TE Part #2-1617088-4
3SAM6015M2 = RELAY



TE Part #CAT-C7901-AL82
COPALUM Sealed: Butt Splices



TE Part #277151-2
TERMINAL,COPALUM R 1/0 3/8



TE Part #ZPF000000000019309
FDBA 56-14-19 SN-K-A499



TE Part #ZPF000000000011583
BJE 66



TE Part #C87423-000
DMVF1679YW2-CS7817

Documents

Product Drawings

[SPICE,SEALED COPALUM 4AL 8CU](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_277164-1_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_277164-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_277164-1_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[COPALUM Lite Sealed Terminals and Splices](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English