

726345-3  ACTIVE

SOLISTRAND

TE Internal #: 726345-3

Closed Ring Tongue Terminal, 4 AWG, M10 Stud, 10.5 mm [.413 in]

Stud Diameter, Closed Barrel, Straight, Tin Plating, Uninsulated

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **33100 – 52600 CMA**

Stud Size: **M10**

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	8.12 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	250
--------------------	-----

Packaging Method	Box
------------------	-----

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
----------------------------	-----------------------------

Stud Size	M10
-----------	-----

Sealable	No
----------	----

Wire Insulation Support Retention Type	Non-Insulation Support
--	------------------------

Contact Features

Barrel Type	Closed
-------------	--------

Terminal Orientation	Straight
----------------------	----------

Terminal Plating Material	Tin
---------------------------	-----

Dimensions

Wire Size	33100 – 52600 CMA
Stud Diameter	10.5 mm [.413 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	26 mm [1.023 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on'

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 726345
SOL RING TONGUE

Customers Also Bought



TE Part #6609044-1
3VW1=F7254 SO



TE Part #1-640454-4
14P MTA100 HDR ASSY SQ STR POL



TE Part #280756-4
FF 375 REC 3-6MM2 TPPB



TE Part #5-1625867-0
RP 1J 0.166W 20R 0.1% 25PPM 1K RL



TE Part #2328702-4
4PIN 0.5MMP FPC CONNECTOR,
BACK FLIP LOCK



TE Part #3-640428-6
06P MTA156 CONN ASSY 22AWG RED



TE Part #4-1474654-8
FSN-21A-11



TE Part #160121
SOLIS 12-10 R 10MM



TE Part #3-1609028-1
5FBH3=F8591



TE Part #6-1393234-7
RP421012

Documents

Product Drawings

[SO-RINGZUNGE D46234](#)

English

726345-3

Closed Ring Tongue Terminal, 4 AWG, M10 Stud, 10.5 mm [.413 in] Stud Diameter,
Closed Barrel, Straight, Tin Plating, Uninsulated

