




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**

Wire Size: **509 – 3260 CMA**

Stud Size: **#6, M3.5**

Features

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	.687 g
Insulation Sleeve Color	Red
Stripe Color	Red

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

Stud Size	#6, M3.5
Sealable	No



Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Contact Features

Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	3.68 mm [.145 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	21.79 mm [.858 in]
Compatible Insulation Diameter (Max)	3.56 mm [.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm [.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392021-2 RED BATTERY DAHT KIT 220V (47689-4)	TE Part # 47806-2 DIES PIDG 22-16 DIE SET	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 47386 DAHT PG PIDG 26-16 ASSY
TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	TE Part # 2392021-1 RED BATTERY DAHT KIT 110V (47689-4)	TE Part # 539691-2 ERGO DIE R.B.Y
TE Part # 169404 CERTI-LOK DIE	TE Part # 2063030-1 SDE DIESET, RBY, UL	TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY	TE Part # 525690 DAHT PG PIDG 20-18 ASSY



TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part # 169400
CERTI-LOK FRAME W/O DIES



TE Part # 1-1377173-5
SMP 0-0327043-0




TE Part # 59250
T-HEAD PIDG 26-14 ASSY


Also in the Series | **PLASTI-GRIP**




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)




Spade Terminals(159)




Splices(45)

Customers Also Bought



TE Part #1-111626-9
20, 2MM, 30 DP, LEAD FREE



TE Part #3-1879663-6
H8 249R 0.1% 15PPM



TE Part #GA10K3435STM010
PRO4-OVERMOLDED PROBE




TE Part #7-2176412-7
5W XSM M/OX 5% 7K5



TE Part #T2040164201-000
HE-016-FC




TE Part #165035
PLASTI-GRIP, RING, 12-10 1/4



TE Part #160171
P.G. SPADE



TE Part #3-2176177-1
CRGH0603 1% 47K 0.2W



TE Part #2-1879664-8
[H8 2K21 0.1% 15PPM](#)



TE Part #284377-E
[M12 METAL SHELL, MALE, VERT, 13MM, D8.35](#)

Documents

Product Drawings

[PG SPD 22-16 COMM 22-18 MIL 6](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_327043_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_327043_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_327043_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English

[UL Report](#)

English