




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Keying Plug**

Primary Product Color: **Black**

Operating Temperature (Max): **85 °C [185 °F]**

Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Hardware Accessory Function: **Coding & Keying**

Features

Packaging Features

Packaging Method	Box
Packaging Quantity	2000

Product Type Features

Connector Hardware Accessory Type	Keying Plug
Hardware Accessory Function	Coding & Keying

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5-2337939-8
PCIE GEN4 CON,SMT,164POS,30u",
MYLAR,HT

Also in the Series | AMP ECONOMATE



Connector Contacts(6)



Connector Hardware(2)



Insertion & Extraction Tools(1)



Power Contacts(2)



Standard Edge Connectors(4)

Customers Also Bought



TE Part #1-5147490-0
Next Gen PACE Conn 10 POS 1X2



TE Part #ZPF000000000008043
983-3KE-C 14

Documents

Product Drawings
KEYING PLUG

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_118982-1_K.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_118982-1_K.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_118982-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Instruction Sheets

Instruction Sheet (U.S.)

English

POLARIZING KEY FOR AMP PACE* AND ECONOMATE* I STANDARD PROFILE PRINTED

English