

61018-1 ✓ ACTIVE

## AMP-IN

TE Internal #: 61018-1

Receptacle, PCB Hole Diameter 4.1 mm [.161 in], Through Hole -  
Press-Fit, Pre-Tin Plating, Bag, Terminates To Printed Circuit Board,  
PCB Terminals

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Receptacle**

PCB Thickness (Recommended): **1.6 – 2.39 mm [.063 – .094 in]**

PCB Hole Diameter: **4.1 mm [.161 in]**

Mating Pin Diameter: **1.47 mm [.058 in]**

Profile Height from PCB: **5.33 mm [.212 in]**

## Features

### Product Type Features

Terminal Features	Stud Hole
-------------------	-----------

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]

### Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

### Dimensions

Extension Below Board	3.81 mm [.15 in]
Terminal Material Thickness	.25 mm [.01 in]
PCB Thickness (Recommended)	1.6 – 2.39 mm [.063 – .094 in]
PCB Hole Diameter	4.1 mm [.161 in]
Profile Height from PCB	5.33 mm [.212 in]

### Contact Features

PCB Terminal Type	Receptacle
Mating Pin Diameter	1.47 mm [.058 in]
Terminal Plating Material	Pre-Tin
Terminal Size	Miniature
Terminal Orientation	Straight

### Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Product Terminates To	Printed Circuit Board

### Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 689141-1  
INSERTION TOOL



TE Part # 60986-1  
.058 DIA PIN RECPT L/P



TE Part # 3-60753-2  
.058 DIA PIN TPBR


## Customers Also Bought



TE Part #2007263-1  
SFP+ 1x2 Cage Assembly



TE Part #1761014-3  
SFP 1X2 CAGE ASSY, PRESS FIT



TE Part #282830-3  
TERMI-BLOK PLUG 90&180 3P. 5



TE Part #2834167-3  
RELEASABLE SLIM CONTACT



TE Part #641967-1  
04P UMNL PIN HDR ASSY POL NATL



TE Part #1734577-1  
MOD-JK,8P8C,SHD W/LED, G/Y,6U




TE Part #2-292173-7  
CT BOX HDR H SMT 7P O/TAPE BLA



TE Part #292228-7  
1.5 MINI CT SGL H SMT W/O BOSS



TE Part #640259-1  
058 PIN REC IS 18-22 010TP



TE Part #456868-130-01  
OPT.CONTACT MC3/2 SPRUNG.  
PILTZ FERRULE 2

## Documents

### Product Drawings

[.058 PCB PIN PTPPHBZ](#)

English

---

**CAD Files**[3D PDF](#)

3D

**Customer View Model**[ENG\\_CVM\\_CVM\\_61018-1\\_C\\_c-61018-1-c.2d\\_dxf.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_61018-1\\_C\\_c-61018-1-c.3d\\_igs.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_61018-1\\_C\\_c-61018-1-c.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages****PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS**

English

---

**Product Specifications**[Application Specification](#)

English