

134462-1

✓ ACTIVE

SOLISTRAND

TE Internal #: 134462-1

Closed Ring Tongue Terminal, 2 AWG, 1/4 / M6 Stud, 6.73 mm [.25 in] Stud Diameter, Closed Barrel, Straight, Nickel Plating, Uninsulated

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 52600 – 83700 CMA

Stud Size: 1/4, M6

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	9.66 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Box
------------------	-----

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
----------------------------	-----------------------------

Stud Size	1/4, M6
-----------	---------

Sealable	No
----------	----

Wire Insulation Support Retention Type	Non-Insulation Support
--	------------------------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel

Dimensions

Wire Size	52600 – 83700 CMA
Stud Diameter	6.73 mm [.25 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	38.79 mm [1.527 in]
Barrel Inside Diameter	9.4 mm [.37 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Nickel
Compatible With Wire Plating Material	Nickel

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 134462-1
TERM, RT, STRAT, SOLIS, HR, 8, M10

Customers Also Bought




TE Part #T2113000201-000
HMN-RJ45-F



TE Part #1577647-1
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #T2070244001-000
H24BN-T6



TE Part #1958388-1
STRA,RCT,4,M5,NI



TE Part #1577632-1
TERMINAL RT PIDG PEEK STRATO 18-16 AWG



TE Part #132066-2
TERMINAL SOLISTRAND RING HR 1/0 AWG



TE Part #1577644-1
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #5039254147
DR-25-3/4-0-CS-34034

<p>TE Part #2592494001 SRFR-10/6.5-8-CS-34034</p>	<p>TE Part #5039944010 SRFR-7.8/4.6-8-CS-34034</p>
---	--

Documents

Product Drawings

[TERM, RING, STRAT, HR, SOLIS, 2, M6\(1/4\)](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_134462-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_134462-1_A.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_134462-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English