



Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A**
USB Version: **2.0**
Connector Profile: **Standard**
Connector & Housing Type: **Receptacle**
Number of Ports: **1**

Features

Operation/Application

Assembly Process Feature	None
Circuit Application	Power, Signal & High Speed Data

Contact Features

Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Current Rating (Max)	1.5 A

Industry Standards

Industry Standard	USB 2.0
IP Rating	IP67

Packaging Features

Packaging Quantity	65
Packaging Method	Box

Housing Features

--	--



Housing Color	Black
Housing Material	Zinc Diecast
Body Orientation	Straight

Mechanical Attachment

Locking Feature	With
PCB Mount Location	Cable Mount
PCB Mount Retention Type	None
Connector Mounting Type	Cable Mount (Free-Hanging)

Body Features

Shell Plating Material	Tin over Nickel
Connector Profile	Standard

Product Type Features

USB Adapter Type	A
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
USB Connector Type	USB 2.0 Type-A

Configuration Features

Number of Ports	1
Number of Positions	4

Usage Conditions

Soldering Temperature (Max)	350 °C[662 °F]
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2008618-2
Protective Cover Kit

Also in the Series | Industrial USB IP67



USB Connectors(3)



USB Type A Connectors(3)

Customers Also Bought



TE Part #130046
PIDG RING TONGUE



TE Part #5-102570-5
14 MODII HDR DRRS SHRD LF




TE Part #130005
PIDG R 22-16 10 (5MM)



TE Part #280359
AMPMODU II REC. HSG, SINGLE ROW, 4 POS.



TE Part #181270-3
MOD 2 BUCHSE



TE Part #280708-2
MOD 2 CONTACT



TE Part #2110989-1
EP 2.5 RCPT CONTACT, 26-22 AWG



TE Part #1-103957-2
10X2 MTE RCPT SR LATCH .100CL



TE Part #5-747905-5
9 Rcpt Solder Cup, 30 gold, Ro



TE Part #5-1437567-8
MPG406R=(MSPG) SW PUSHBUTTON

Documents

Product Drawings

Recpt Kit, Series B to A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2058365-1_A_c-2058365-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2058365-1_A_c-2058365-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2058365-1_A_c-2058365-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773463-4_INDUSTRIAL_USB_CONNECTORS

English

CONNECTIVITY SOLUTIONS FOR INFOTAINMENT APPLICATIONS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English