



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Primary Product Material: **Silicone**

Primary Product Color: **Gray**

Operating Temperature (Max): **125 °C [338 °F]**

Operating Temperature Range: **-40 – 180 °C [-40 – 356 °F]**

EU RoHS Compliance: **Compliant**

Features

Packaging Features

Packaging Method	Bag
Packaging Quantity	5000

Body Features

Primary Product Material	Silicone
Primary Product Color	Gray

Usage Conditions

Operating Temperature (Max)	125 °C[338 °F]
Operating Temperature Range	-40 – 180 °C[-40 – 356 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUN 2020
(209)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 344106-1
18W EMS.REC.HSG.ASSY.


Customers Also Bought




TE Part #HDP26-24-14PN
PLG, 14P, BLK, N, 4/12/16, P



TE Part #344111-1
36W EMS.REC. HSG.ASSY



TE Part #CAT-AM705-CH8173
AMP Unsealed Connector Housing



TE Part #1564411-2
SLIDE,TAB HSG GROUP E



TE Part #6473423-1
SUPER SEAL 26POS CAP ASSY H AU

TE Part #T2020002008-000
CDF-0.75

TE Part #2278600-3
52POS., MIXED REC. HSG+LEVER, ASS'Y

TE Part #881590-1
ECONOSEAL TAB .070

TE Part #345259-1
ANTI-BACKOUT 6WAY TAB
HSGECONO

Documents

Product Drawings
ECON 3 LC PLUG SILIC

English

CAD Files
Customer View Model
ENG_CVM_348461-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_348461-1_A.3d_stp.zip

English

Customer View Model
ENG_CVM_348461-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Product Datasheet

English