



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover Assembly**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PBT GF30**

EU RoHS Compliance: **Compliant**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover Assembly
---	----------------

Mechanical Attachment

Strain Relief	Without
---------------	---------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF30

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2005244-2  
025/110/250 38P COVER HSG BLK

Customers Also Bought



TE Part #2005388-6  
JPT SLD 2P PLUG ASSY-1S BLK



TE Part #2109220-2  
.64/2.8 HYB 12P SLD PLUG ASM



TE Part #2188225-1  
020/060 28P PLUG ASSY(CODE A1)



TE Part #2219639-7  
020/060 38P PLUG ASSY GRN






TE Part #2219642-8  
020/060 32P PLUG ASSY BLU



TE Part #2309585-2  
025/060/110 HYB26P SLIDER COVER ASSY



TE Part #2328991-9  
MATENET 1PORT PLUG HSG



TE Part #1897212-1  
MCP 1.5 2P PLUG ASSY



TE Part #2309513-2  
51POS,HYBRID,REC HSG ASSY,SLD

TE Part #8-2188321-1  
C.E BOX ASSY-BA I/P SJB(LHD)

Documents

Product Drawings

025/110/250 38P COVER ASSY BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2005243-2\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2005243-2\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2005243-2\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

CAVITY PLUG (HYB 38P ISL PLUG)

English