




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > HE13/HE14 IDC Receptacle, SRRA, AWG26



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **2.54 mm [.1 in]**

[All HE13/HE14 IDC Receptacle, SRRA, AWG26 \(3\)](#)

Features

Electrical Characteristics

Insulation Resistance	1000 MΩ
-----------------------	---------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Tube
------------------	------

Contact Features

Contact Underplating Material	Nickel
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Current Rating (Max)	3 A

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without



Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Compatible Insulation Diameter Range	1 mm[.039 in]
Connector Height	14.5 mm[.571 in]
Wire Size	26 AWG
Connector Length	13.5 mm[.531 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Housing Features

Housing Material	PBT GF
Housing Entry Configuration	Both Ends Closed
Centerline (Pitch)	2.54 mm[.1 in]

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1

Body Features

Primary Product Color	Blue
-----------------------	------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 281695-5
HEADER HE14 STRAIGHT 5 P



TE Part # 281698-5
HEADER HE14 RA 5 P


Also in the Series | AMPMODU HE 13/HE 14



Connector Contacts(4)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(66)




Wire-to-Board Connector Assemblies & Housings(58)



Wire-to-Board Headers & Receptacles (66)

Customers Also Bought




TE Part #1-111506-8
016 UNIV I/O 30DP SLOT LTCH



TE Part #163304-2
MATENLOK SOCKET SDW




TE Part #163305-2
MATENLOK PIN SDW




TE Part #643071-3
03P MTA156 FD-THRU COVER



TE Part #826632-2
2P AMPMODU II II PIN HDR




TE Part #643071-7
07P MTA156 FD-THRU COVER




TE Part #2176083-5
EP 5W (S) 47R 5%



TE Part #CONSMA002
SMA RA Jack 50 Ohm PCB Through Hole



TE Part #640551-4
04P MTA156 COVER



TE Part #3-2176524-6
3503G 2B 1K27 1% 1K RL

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_281711-5_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_281711-5_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_281711-5_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English