

25AYA6A

! PENDING OBSOLESCENCE

Corcom | Corcom AYA

TE Internal #: 6609977-2

TE Internal Description: 25AYA6A = F7746A

3 Phase Filters, Corcom AYA Series

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters > 3 Phase Filters, Corcom AYA Series



Current Rating: 25 A

Input Termination Type: Stud

Output Termination Type: Stud

Wiring Configuration: WYE (4 wire + ground)

Operating Voltage: 440 VAC

[All 3 Phase Filters, Corcom AYA Series \(0\)](#)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Stud
Output Termination Type	Stud

Electrical Characteristics

Leakage Current (Max) (250VAC, 50Hz)	2.82 mA
Current Rating	25 A
Operating Voltage	440 VAC

Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-AY61
[3 Phase Filters, Corcom AYO Series](#)



TE Part # CAT-C8114-A11
[EMI Filter Accessories, Corcom A Series](#)

Also in the Series |

Customers Also Bought





TE Part #1-6609032-8
20VR1=F7210 S0




TE Part #206060-1
CPC PLUG ASSEMBLY SIZE 11-4



TE Part #5-534206-7
14 MODII VRT DR CE 100/115



TE Part #4-2176337-0
CRGCQ 0402 18K 1%



TE Part #7-2176314-5
MELF SMA-A 33R 1% 50PPM 0102 0.3 W



TE Part #928820-1
STD TIMER CONTACT



TE Part #4-1625826-2
TL2B R018 1% 4K RL



TE Part #177103-000
44AM1131-16-MST3-9CS2275



TE Part #2-2176456-2
CPF 0603 1R65 0.1% 25ppm 1K RL



TE Part #770178-2
06P MINI-UMNL ASSY VO SNAU

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6609977-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6609977-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6609977-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_Corcom_Product_Guide_AYA_Series

English

Datasheet - Ev-Charging Passives

English



Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English