




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 33100 – 52600 CMA

Stud Size: 1/4, M6

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Tape Mounted

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4, M6
Sealable	No
Wire Insulation Support Retention Type	Insulation Support



Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	33100 – 52600 CMA
Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	49.48 mm[1.948 in]
Compatible Insulation Diameter (Max)	13.08 mm[.515 in]
Compatible Insulation Diameter Range	13.08 mm[.515 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 1490536-1
HYP10 PLASTI-GRIP 4AWG DIE SET

Also in the Series | PLASTI-GRIP




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(159)



Splices(45)

Customers Also Bought





TE Part #167292-1
09P.HDP20 PLUG ASSY



TE Part #539635-1
ERGO HAND TOOL FRAME W/O DIES




TE Part #53245-1
TERMINAL,PG SPR SPD 16-14 10



TE Part #794059-1
MINI UMNL PIN L/P



TE Part #794758-1
MINI UMNL WIRE SEAL,18-26AWG



TE Part #788159-1
SLD CPC 13-9 RCPT,STD,SM INS



TE Part #2063567-1
SDE MCP4.8K 1.1-3.0mm2 ASSY



TE Part #60-0251-011-P00
CONTACT SOCKET 1 MM



TE Part #61-0252-011-P00
CONTACT PIN 0.6 MM



TE Part #61-0231-011-P00
CONTACT PIN 1 MM

Documents

Product Drawings

TERMINAL R PG 4 1/4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_52043-5_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_52043-5_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_52043-5_P.3d_stp.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_52043-5_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_52043-5_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_52043-5_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English