

RN73C1J10KBTDF

✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 4-1614349-2

Surface Mount Precision Resistor, Thin Film, 0603, .063 W, 10K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Height .45 mm [.018 in], Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0603

Power Rating: .063 W

Resistance Value: 10K Ω

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Electrical Characteristics

Operating Voltage	50 V
Power Rating	.063 W
Resistance Value	10K Ω
Resistance Class	1kΩ – 1MΩ
Passive Component Tolerance	.1 %

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions



Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RN73C1J10KBTDF

Surface Mount Precision Resistor, Thin Film, 0603, .063 W, 10K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Height .45 mm [.018 in], Holsworthy RN73



TE Part # 1-1676142-3

RN 0805 100K 0.01% 10PPM 5K RL

TE Part # 1614349-9

RN 0603 10K 0.1% 10PPM CUT LENGTH

TE Part # 1676153-2

RN 0805 10K 0.1% 10PPM 1KRL

TE Part # 1676153-3

RN 0805 10K 0.1% 10PPM 5KRL

TE Part # 8-1879130-4

RN 0402 5K11 0.1% 10PPM 5K RL

Also in the Series | [Holsworthy RN73](#)

[Surface Mount Resistors\(3641\)](#)

Customers Also Bought

TE Part #1658694-6

A/L UNIV HDR 10P ACT PIN

TE Part #6-1879135-5

RN 0603 5R49 0.1% 10PPM 5K RL

TE Part #3-2176089-9

RP 1J 0.166W 28K 0.1% 25PPM 1K RL

TE Part #2176392-6

RQ 1206 150K 0.1% 10PPM 5K RL

TE Part #6-1879131-8

RN 0402 10K 0.1% 10PPM 1K RL

TE Part #8-1879125-6

RN 0402 100R 0.1% 10PPM 1K RL

TE Part #4-1879133-0

RN 0603 2K21 0.1% 10PPM 1K RL

TE Part #1879125-2

RN 0402 51R1 0.1% 10PPM 1K RL

RN73C1J10KBTDF

Surface Mount Precision Resistor, Thin Film, 0603, .063 W, 10K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Height .45 mm [.018 in], Holsworthy RN73



Documents

Product Drawings

RN 0603 10K 0.1% 10PPM 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1614349-2_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1614349-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1614349-2_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

High Precision Resistors (SMD) - Type RN73 Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English