




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Dimensions

Product Length	20.32 mm[.8 in]
Compatible Insulation Diameter Range	3.1 – 4.1 mm[.12 – .16 in]
Terminal Material Thickness	.81 mm[.032 in]



Wire Size

.82 – 2.08 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 641256-1
BLADE TAB 250 18-14AWG BR LP

TE Part # 90165-1
DAHT 250 FASTON REC 18-14 ASSY

TE Part # 58524-2
PROCrimper DIE

TE Part # 153259-3
FF 250 REC TPBR FOR PCB LP

TE Part # 58524-1
PROCrimper TOOL & DIE

TE Part # 1-1579007-4
EXTRACTION TOOL

TE Part # 4-1579007-3
EXTRACTION TOOL KIT

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(207)

Insertion & Extraction Tools(2)

PCB Terminals(2)

Quick Disconnects(250)

Customers Also Bought



TE Part #11027286-00
44008RC,THERM,ROHS




TE Part #5-1625971-3
HSA25 4K7 5%



TE Part #3-2176057-5
RLP73K 3A R27 1% 1K RL




TE Part #1879075-3
THS25 R05 5%




TE Part #796096-2
SLD CPC RCPT ASY,11-4,STD SEX




TE Part #61944-1
250 FASTON REC 18-14 AWG BR




TE Part #61300-1
SPLICE IS 10000-16000 .031 TPST



TE Part #1-2176331-4
CRGP 2512 120R 1%



TE Part #796276-1
SLD CPC RCPT ASSY,17-16,STD SX



TE Part #9-2176422-0
TLRP 2512 3.0W R050 1% 75PPM 4K RL

Documents

Product Drawings

FF 250 REC 18-14AWG BR LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42282-1_AL_c-42282-1-al.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42282-1_AL_c-42282-1-al.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42282-1_AL_c-42282-1-al.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



FASTIN_FASTON_Product_Line

English

Product Specifications

Application Specification

English